

AMPHENOL RF PART NUMBER

031-4774-5

BNC Straight Clamp Triax Plug for RG-307 Triax

Amphenol® RF



PRODUCT IMAGE
COMING SOON

PRODUCT OVERVIEW

RF Connector, BNC Straight Clamp Triax Plug for RG-307 Triax

Product Type	Connectors
Product Series	Triax
Status	Active

PRODUCT SPECIFICATIONS

Gender	Plug
Orientation	Straight
Termination Style	Cable - Clamp
Impedance (Ohms)	75
Body Finish	Silver
Body Material	Brass
Contact Finish	Silver
Contact Material	Beryllium Copper
Contact Termination Style	Solder
Insulator Material	PTFE
Cable Group	Special
Cable Type	RG-307 Triax
Coupling Mechanism	Bayonet
Max Frequency (GHz)	0.5
Polarity	Standard
Min. Temp. (Celsius)	-65
Max. Temp. (Celsius)	165

PRODUCT COMPLIANCE

Product compliance documentation, if available is listed below:

RoHS 2 (EU)	Compliant with Exemption 6C
-------------	-----------------------------