

AMPHENOL RF PART NUMBER

## 031-30231-77

Triax BNC Clamp Plug

Amphenol® RF



PRODUCT IMAGE  
COMING SOON

### PRODUCT OVERVIEW

RF Connector, Triax BNC Clamp Plug

Product Type	Connectors
Product Series	Triax
Status	Active

### PRODUCT SPECIFICATIONS

Gender	Plug
Orientation	Straight
Termination Style	Cable - Clamp
Impedance (Ohms)	Non-Constant
Body Finish	Nickel
Body Material	Brass
Contact Finish	Gold
Contact Material	Brass
Contact Termination Style	Solder
Insulator Material	PTFE
Cable Group	Special
Coupling Mechanism	Bayonet
Max Frequency (GHz)	0.5
Polarity	Standard
Min. Temp. (Celsius)	-65
Max. Temp. (Celsius)	165
Mating Cycles	500

---

## PRODUCT COMPLIANCE

Product compliance documentation, if available is listed below:

RoHS 2 (EU)	Compliant with Exemption 6C
-------------	-----------------------------