

AMPHENOL RF PART NUMBER

901-9244-2SF

SMA Straight Jack, Panel Mount, Solder Cup, 50 Ohm

Amphenol® RF



PRODUCT IMAGE
COMING SOON

PRODUCT OVERVIEW

RF Connector, SMA Straight Jack, Panel Mount, Solder Cup, 50 Ohm

Product Type	Connectors
Product Series	SMA
Status	Active

PRODUCT SPECIFICATIONS

Gender	Jack
Orientation	Straight
Termination Style	Solder Cup
Impedance (Ohms)	50
Body Finish	Passivated
Body Material	Stainless Steel
Contact Finish	Gold
Contact Material	Beryllium Copper
Contact Termination Style	Solder
Insulator Material	PTFE
Coupling Mechanism	Threaded
Mounting Feature	2-Hole Flange
Max Frequency (GHz)	18
Polarity	Standard
Extended Dielectric	Extended Dielectric
Extended Dielectric Length (Inches)	0.025
Thread Direction	Standard

Min. Temp. (Celsius)	-65
Max. Temp. (Celsius)	165
Mating Cycles	100

PRODUCT COMPLIANCE

Product compliance documentation, if available is listed below:

RoHS 2 (EU)	Compliant with Exemption 6C
-------------	-----------------------------