

<p>Fig. 1</p> <p>SMA Bulkhead Jacks Solder to Body Solder Center Contact Gold Plated <b>901-9210-1</b> for .141" (3.6mm) S/R RG-402 (M17/130) <b>901-9210-2</b> for .085" (2.2mm) S/R RG-405 (M17/133)</p>	<p>Fig. 2</p> <p>SMA Bulkhead Jacks Braid Crimp Captive Contact Solder Center Contact <b>901-9610-1SF▲</b> Passivated for RG-55B, 142B, 223, 400 <b>901-9610-3▲</b> Gold Plated <b>901-9610-3SF▲</b> Passivated for RG174, 179, 187, 188, 316 <b>901-9610-12SF</b> Passivated for Double Braid RG-316 <b>901-10015</b> Passivated for LMR 240</p>	<p>Fig. 3</p> <p>SMA Bulkhead Jacks Braid Crimp Solder Center Contact <b>901-10021-1SF▲</b> Passivated for RG-55B, 142B, 223, 400 <b>901-10021-3SF▲</b> Passivated for RG174, 179, 187, 188, 316 <b>901-10021-12SF</b> Passivated for Double Braid RG-316</p>
--	---	---

## SMA BULKHEAD JACKS FOR SEMI-RIGID & FLEXIBLE CABLES – 50Ω Impedance

Cable RG-/U	Cable Attachment		Dimensions In. (mm)		CAI	Plt.	Ins.	Notes	Amphenol Number	Fig.
	Outer	Inner	a	c						
<b>.085" (2.2mm) Semi-Rigid RG-405 (M17/133)</b>	Solder to Body	Solder	.750(19.1)	.090(2.3)	C47	P9	D1	—	<b>901-9210-2</b>	1
<b>.141" (3.6mm) Semi-Rigid RG-402 (M17/130)</b>	Solder to Body	Solder	.750(19.1)	1.44(3.7)	C47	P10	D1	—	<b>901-9210-1</b>	1
<b>55, 142, 223, 400</b>	Crimp	Solder	1.50(38.1)	.220(5.6)	C56	P13	D1	Capt. Contact	<b>▲ 901-9610-1SF</b>	2
	Crimp	Solder	1.50(38.1)	.220(5.6)	C56	P13	D1	Non Capt. Contact	<b>▲ 901-10021-1SF</b>	3
<b>174, 179, 187, 188, 316</b>	Crimp	Solder	1.50(38.1)	.128(3.3)	C56	P11	D1	Capt. Contact	<b>▲ 901-9610-3</b>	2
	Crimp	Solder	1.50(38.1)	.128(3.3)	C56	P11	D1	Non Capt. Contact	<b>▲ 901-10021-3SF</b>	3
	Crimp	Solder	1.50(38.1)	.128(3.3)	C56	P13	D1	Capt. Contact	<b>▲ 901-9610-3SF</b>	2
<b>Double Braid 316</b>	Crimp	Solder	1.50(38.1)	.128(3.3)	C56	P13	D1	Non Capt. Contact	<b>▲ 901-10021-12SF</b>	3
	Crimp	Solder	1.50(38.1)	.142(3.6)	C56	P13	D1	Capt. Contact	<b>901-9610-12SF</b>	2
<b>LMR 240</b>	Crimp	Solder	1.08(27.4)	.261(6.6)	C56	P13	D1	Capt. Contact	<b>901-10015</b>	2

▲ distributor stocked