

AMPHENOL RF PART NUMBER

## 082-5370-1005

N-Type Straight Crimp Plug for RG-55, RG-55A, RG-55B, RG-142, RG-223, 50 Ohm

Amphenol® RF



PRODUCT IMAGE  
COMING SOON

### PRODUCT OVERVIEW

RF Connector, N-Type Straight Crimp Plug for RG-55, RG-55A, RG-55B, RG-142, RG-223, 50 Ohm

Product Type	Connectors
Product Series	N-Type
Status	Active

### PRODUCT SPECIFICATIONS

Gender	Plug
Orientation	Straight
Termination Style	Cable - Crimp
Impedance (Ohms)	50
Body Finish	Nickel
Body Material	Brass
Contact Finish	Gold
Contact Material	Brass
Contact Termination Style	Crimp
Insulator Material	PTFE
Cable Group	C1
Cable Type	RG-142, RG-223, RG-304, RG-400, RG-55
Crimp Tool	CTL-3
Coupling Mechanism	Threaded
Max Frequency (GHz)	11
Polarity	Standard

Thread Direction	Standard
Min. Temp. (Celsius)	-65
Max. Temp. (Celsius)	165
Mating Cycles	500

---

## PRODUCT COMPLIANCE

Product compliance documentation, if available is listed below:

RoHS 2 (EU)	Compliant with Exemption 6C
-------------	-----------------------------