

Products

- [7/16](#)
- [1.0/2.3](#)
- [1.6/5.6](#)
- [AFI](#)
- [AMC](#)
- [BNC / RP-BNC](#)
- [C](#)
- [FAKRA SMB](#)
- [FME](#)
- [HN](#)
- [MCX](#)
- [Mini-UHF](#)
- [Mini 75 Ohm SMB](#)
- [MMCX](#)
- [Precision \(APC\)](#)
- [QDS](#)
- [QMA](#)
- [QWS](#)
- [SC](#)
- [SlimLine BNC](#)
- [SMA / RP-SMA](#)
- [SMB](#)
- [SMC](#)
- [SMP](#)
- [SSMB](#)
- [TNC / RP-TNC](#)
- [Triax](#)
- [Twin BNC](#)
- [Twinax](#)
- [Type F](#)
- [Type G](#)
- [Type N](#)
- [UHF](#)

-
- [Adapters](#)
- [Cable Assemblies](#)
- [Tools](#)
- [Accessories](#)
-
- [Product Search](#)
-
- [Inventory Search](#)

product search



Search Results for: 901-9601-3
Results: 1 - 2 of 2



Part Number: 901-9601-3
Connector Type: Cable
Contact: Pin
Impedance: 50 Ohm
Cable: RG 174, 188A, 316, Belden 7805A

Product Type: Connector
Product Series: SMA
Body Style: Straight
Termination: Crimp/Solder

[View Details](#) | [Product Specs](#) | [Assembly Instructions](#) | [Customer Drawing](#) | [Distributor Inventory](#)



Part Number: 901-9601-3SF
Connector Type: Cable
Contact: Pin
Impedance: 50 Ohm
Cable: RG 174, 188A, 316, Belden 7805A

Product Type: Connector
Product Series: SMA
Body Style: Straight
Termination: Crimp/Solder

[View Details](#) | [Product Specs](#) | [Assembly Instructions](#) | [Customer Drawing](#) | [Distributor Inventory](#)

Results: 1 - 2 of 2