



BNC CAPS & ACCESSORIES

| Description | Dimensions, inches (millimeters) | | | | Notes | | Military Number | Amphenol Number | Fig. | |
|---|----------------------------------|-------------|------------|-----------|------------|------|-----------------|-----------------|---------------|---|
| | a | b | c | e | Pt. | Ins. | | | | |
| Male Cap & Chain Resistor Terminated, 1% 1/2watt | 50Ω | 1.19(30.2) | .562(14.3) | .144(3.7) | 3.50(88.9) | P1 | D1 | — | 35650-51* | 1 |
| | 75Ω | | | | | P1 | D1 | — | 35650-75* | 1 |
| | 51Ω | | | | | P1 | D6 | MX-554 | 4700-51** | 1 |
| Male Cap, Resistor Terminated, 1% 1 watt | 51Ω | 1.12(28.6) | .562(14.3) | — | — | P1 | D1 | — | 46650-51* | 2 |
| Male Cap, Resistor Terminated, 1% 1 watt | 50Ω | 1.11(28.1) | .571(14.5) | — | — | P1 | D23 | — | 46650-51RFX | 3 |
| | 75Ω | | | | | | | | 46650-75RFX | 3 |
| | 93Ω | | | | | | | | 46650-93RFX | 3 |
| Male Cap & Chain | | .688(17.5) | .563(14.3) | .130(3.3) | 2.25(57.2) | P3 | — | CW-123/U | 31-6* | 4 |
| Male Shorting Cap & Chain | | .688(17.5) | .563(14.3) | .144(3.7) | 2.50(63.5) | P1 | — | CW-159/U | 31-17* | 5 |
| Male Shorting Cap | | .594(15.1) | .563(14.3) | — | — | P1 | — | — | 5275* | 6 |
| Pkg. of 25 Lugs Used Inside Panel on Front Mount Bulkhead Receptacles to Ground Cable Shield* | | .961(24.4) | .578(14.7) | — | — | P3 | — | (IBM 2245373) | 31-759* | 7 |
| Pkg. of 25 Lugs Used Inside Panel on Front Mount Bulkhead Receptacles for Ground Wire to Circuit | | 1.156(29.4) | .578(14.7) | — | — | P8 | — | — | 31-10152-RFX* | 8 |

■ IBM 3110787 * recognized under the component program of U.L., Inc. ▲ distributor stocked