## PRODUCT DATASHEET

# NiMH Battery Charger (CH15MN)

## **VERSATILE**

 Charges 1 to 4 AA or AAA NiMH batteries



## **COMPACT**

 Charger and AC adapter small, sleek design



## **MOBILE**

· Includes car adapter



## **FAST**

 Batteries ready for use in 15 minutes (2200 mAh AA)



### **SMART**

 Automatically detects battery size and has LED indicators



## 15 Minute Charger



#### **Before Using Your Charger:**

Please read all instructions and cautionary markings on the battery charger, batteries, and device.

## Best used with Energizer NiMH batteries.

Note: Batteries may become hot to the touch while charging.

## **North American Region**

**Download Instructions and Warranty Information** 

English | Français | Español

## **Product Detail:**

**Designation:** 15 Minute Charger

Color: Charcoal Grey

Charge Capability: "AA" (1) to (4) "AAA" (1) to (4) Charge Duration: Primary = 20 minutes Secondary = 24 hours

Charging Current: "AA" Primary = 7500 mA

"AA" Secondary = 100 mA
"AAA" Primary = 2850 mA
"AAA" Secondary = 35 mA

Charging Times: (estimated)

| Battery | Capacity  | Estimated |
|---------|-----------|-----------|
| (NiMH)  | (mAh)     | (time)*   |
| AA      | 2500-2650 | 19 min    |
| AA      | 2450      | 18 min    |
| AA      | 2200      | 16 min    |
| AA      | 2000      | 14.5 min  |
| AAA     | 1000      | 19 min    |
| AAA     | 900       | 17 min    |
| AAA     | 850       | 15 min    |

Shutoff Mechanism: Delta V Detection

Temperature Detection

**Timer Control** 

Charger Input: DC 11-16V, 5A

AC Adapter Input: 120vac~60Hz, 85W

Weight (charger): 180 grams (6.3 oz.)

Dimensions (mm): 40 x 131 x 78 (H x L x W)

Rev Polarity Protection: Yes Primary Battery Detection: Yes

#### Important Notice

This datasheet contains information specific to products manufactured at the time of its publication.

© Energizer Holdings, Inc.

Contents herein do not constitute a warranty.



<sup>\*</sup> Per American National Standards Institute (ANSI) standard.