

Home Application

Product Search

Product Home Specifications

lanuals

Products

Where To Buv

What's New

Suppor

About Us

FLUKE:

Accessories > Current Clamps >

i400s AC Current Clamp

Nominal current range:	40 A Range 0.5 A to 40 A 400 A Range5 A to 400 A
Basic accuracy:	40 A Range 2% + 0.015 A (45-400 Hz) 400 A Range2% + 0.04 A (45-400 Hz)
Phase Shift:	40 A Range 0.5 to 1 A Unspecified 1 A to 5 A 4° 5 A to 10 A 3° 10 A to 20 A 3° 20 A to 40 A 2° 40 A to 400 ANA 400 A Range 0.5 to 1 A NA 1 A to 5 A NA 5 A to 10 A Unspecified 10 A to 20 A 2° 20 A to 40 A 2° 40 A to 400 A1.5°
Typical Bandwidth:	40 A Range 5 Hz - 10 kHz 400 A Range5 Hz - 10 kHz
Output level(s):	40 A Range 10 mV/A 400 A Range1 mV/A
Crest Factor:	40 A Range ≤ 3 400 A Range≤ 3 to 300 A ≤ 2.5 to 400 A

Safety	CAT IV 600 V, CAT III, 1000 V
Maximum Non- Destructive Current	1000 V AC

Warranty	1 year
Maximum conductor size	32 mm (1.25 inches)
Output cable length	2.5 m (8.2 ft)
BNC Adapter	Yes
Dimensions	150 x 70 x 30 mm
Weight	114 g