



Accessories > Cables & Hardware >

884X-ETH Ethernet Interface Cable

[Product Home](#)

[Manuals](#)



- 8-conductor (4 twisted pair) unshielded cable (48 inches) with an 8-position modular plug (RJ45) on each end, with an overmold boot/strain relief
- Rated working voltage: 100 V rms maximum
- Operating temperature range: -40 °C to +80 °C

Model Name	Description
884X-ETH	Ethernet Interface Cable