

Products

Where To Buy

What's New

Suppor

About Us

Digital Multimeters >

Product Search

Features Specifications Models, Pricing, Options,

Manuals Product Registration Extended Specifications Data Sheet

Fluke 170 Series Digital Multimeters

| Voltage DC | 175 - Accuracy* ± (0.15%+2) 177 - Accuracy* ± (0.09%+2) 179 - Accuracy* ± (0.09%+2) Max. Resolution0.1 mV Maximum 1000 V |
|-------------|--|
| Voltage AC | Accuracy* ± (1.0%+3) Max. Resolution0.1 mV Maximum 1000 V |
| Current DC | Accuracy* ± (1.0%+3) Max. Resolution0.01 mA Maximum 10 A |
| Current AC | Accuracy* ± (1.5%+3) Max. Resolution0.01 mA Maximum 10 A |
| Resistance | Accuracy* \pm (0.9%+1) Max. Resolution0.1 Ω Maximum 50 M Ω |
| Capacitance | Accuracy* ± (1.2%+2) Max. Resolution1 nF Maximum 10,000 μF |
| Frequency | Accuracy* ± (0.1%+1) Max. Resolution0.01 Hz Maximum 100 kHz |
| Temperature | 179 - Accuracy* ± (1.0%+10) Max. Resolution0.1°C Range -40°C/400°C |
| Note | *Accuracies are best accuracies for each function |

| Operating temperature | -10°C to +50°C |
|---------------------------------|--|
| Storage temperature | -30°C to +60°C |
| Humidity (Without Condensation) | 0% - 90% (0°C - 35°C) 0% - 70% (35°C -50°C) |

| Overvoltage category | EN 61010-1 to 1000 V CAT III. EN 61010-1 to 600 V CAT IV. |
|----------------------|--|
| Agency Approvals | UL, CSA, TÜV listed and VDE Pending |

| Size | 43 x 90 x 185 mm |
|--------|------------------|
| Weight | 420 g |
| | |

| Warranty | Lifetime |
|--------------|--|
| Battery life | Alkaline:~200 hours typical, without backlight |

© 1995 - 2005 Fluke Corporation Privacy Statement