

1-19.99V, 9.999A Switching DC Power Supply Model 1665



The 1665 Switching DC Power Supply uses new switching technologies to offer more power at a lower cost than traditional linear power supplies.

- Over voltage protection
- Constant voltage operation
- Constant current operation (current limiting)
- Easy-to-use
- Bright easy to read LED displays



Models 1665, 1666 & 1667

DC Regulated Power Supplies

Data Sheet

DC Regulated **Power Supplies**

Model 1665, 1666, 1667

- Over voltage protection, short circuit temperature
- Constant voltage operation
- Constant current operations
- Presetting current limiting value



Model 1666

Specifications			Models
	1665	1666	1667
Output Voltage:	I-20VDC	I-40VDC	I-60VDC
Output Current:	0-10A	0-5A	0-3.3A
Ripple & Noise:	20mV	20mV	20mV
Load Regulation:	0.5%+200mV	0.5%+100mV	0.5%+100mV
Line Regulation:	20mV	20mV	20mV
Input Voltage:	90-265VAC, 50/60Hz		
Meter Type:	3 ^{1/2} Digital LED		
Meter Accuracy:	1%+2 counts		
Dimension (HxWxD):	4.5" x 8" x 10.8"		
Weight:	6.6 lbs		