

Switching DC Power Supply with USB Charger Output 1-36V, 0-3A Model 1550



The model 1550 is a compact 108 watt power supply delivering 1-36V and 0-3A from its main isolated output. A unique feature of the 1550 supply is the USB charging port located on the front panel allowing the user to charge a cell phone or MP3 player. Clean power and quiet operation make this power supply ideal for laboratories, work shops, and schools where bench space is limited.

- USB Charging port on front panel*
- Rear panel security loop
- Compact design
- Output On/Off control
- Large bright easy to read LCD display
- Constant voltage and constant current operation
- Overvoltage protection

*= Charging port is USB 1.1 & 2.0 compatible. It will not charge USB 2.0 only devices.

Data sheet

Switching DC Power Supply with USB Charger Output 1-36 V, 0-3 A

Model 1550



The model 1550 is a compact 108 watt power supply delivering 1-36 V and 0-3 A from its main isolated output. A unique feature of the 1550 supply is the USB charging port located on the front panel allowing the user to charge a cell phone or MP3 player. Clean power and quiet operation make this power supply ideal for any bench in laboratories, work shops and schools where bench space is limited.

Features:

- USB charging port on front panel*
- Rear panel security loop
- Compact design
- Output On/Off control
- Large bright easy to read LCD display
- Constant voltage and constant current operation
- Overvoltage protection
- * Charging port is USB 1.1 & 2.0 compatible. It will not charge USB 2.0 only devices.

USB Charging Port	
Charge your cell phone or MP3 player while you work	

Specifications	model
	1550
MAIN OUTPUT	
Output Voltage Adjustable Range	1.0 – 36 VDC
Output Current Adjustable Range	0 – 3 A
Voltage Regulation	
Load from 10 % to 100 %	±50 mV
Line from min to max	±20 mV
Ripple (rms)	±5 mV
Noise (Peak to Peak)	±50 mV
Current Regulation	
Load from 10 % to 100 %	±20 mA
Line from min to max	±20 mA
Switching Operation Frequency	80 kHz to 120 kHz
Efficiency at Max Power	83 % (±10 %)
Voltmeter and Ammeter Display	3 Digit
Voltmeter Accuracy	±1 % of rdg. ± 5 digits
Ammeter Accuracy	± 1 % of rdg. \pm 5 digits
usb оитрит	
Output Voltage	5 V (±10 %)
Output Current	400 mA (±10 %)
Load Voltage Regulation	80 mV (±10 %)
Ripple & Noise (no load rms)	8 mV (±10 %)
GENERAL	
Input Voltage	100 − 120 Vac (50~60 Hz)
	For 220V input version order model number
	1550EXD
Full Load Input Current at 120 Vac	1.8 A (±10 %)
LCD Indication	CC, CV, Amp, Volt, Output ON-OFF
Protection	Short Circuit, Overload, Over Temperature,
	Over Voltage
Cooling System	Natural Convection
Dimensions (WxHxD)	2.8" x 6.0" x 9.8" (70 x 150 x 250 mm)
Weight	4.4 Lbs. (2 kgs)
	One Year Warranty

Supplied: User Manual, Power Cord

Rear Panel Security Loop

Secure the power supply to a work station to prevent unwanted removal



