speco technologies



contact category search

products

new products



software downloads

how to use search

reference

home




Color Tamperproof Dome Camera (CVC-647TP)

Speco Technologies' smaller color vandal resistant dome camera is designed for high performance at a lower price. It has the best cost/performance ratio while being able to withstand hits from a 10 lb. sledge hammer. Available with black or white housing.

Technical Specifications

Resolution	420 TV lines horizontal
Image Device	Sony 1/4" Super HAD* CCD Sensor
Illumination	0.5 lux, F2.0
Electronic Shutter	1/60 - 1/100,000 second
Output	1 Vp-p/75 ohms (BNC Connector)
Lens	Board lens F3.6mm/F2.0, optional lenses available
S/N Ratio	More than 50db
Consumption Current	120ma
Operating Temperature	-10 degrees C to 50 degrees C (14 degrees F to 122 degrees F)
Power Supply	12 V DC power supply (UL listed) included
Dimensions	4" Diameter x 2.5" High
Weight	10.5 oz.

Downloads



©2005 Speco Technologies, All Rights Reserved