



new products

corporate news

software downloads

how to use search

reference

home

products



Color Wall Mount Camera with Audio (CVC-691AM/W)

Our 1/3" CCD color wall mount with audio has a compact weather resistant white ABS plastic housing. It is ideal for mounting in office areas, lobbies, hallways, inside buses, building exteriors and residential entrances. It has a 1.0 lux with 350 line resolution. It features a 3.6mm wide angle lens and a built-in electronic shutter. It uses an RCA female video output. A BNC adapter and 12V DC power supply is also included. A B/W version of his camera can be found under model number CVC-91AM/W.

Technical Specifications

Audio Output Level	300mV at 600 ohm
Dimensions	1.75"L x 2.25"W x 2.75"H
Electronic Shutter	auto 1/60-1/100,000 seconds
Housing	White ABS molded plastic
Humidity	Within 95 % RH
Image Device	1/3" color CCD image sensor
Lens	3.6mm, Hor. 74°, Vert. 57°
Lens Options	6, 8mm
Minimum Illumination	1.0 lux
Number of Pixels	512 horizontal x 492 vertical
Operating Temperature	14° F - 122° F
Outputs	Video/Audio - RCA with BNC adapter, power - DC jack
Power Consumption	210 mA
Power Supply	regulated 12V DC power supply included (UL and CSA listed)
Resolution	350 lines
Scanning Frequency	horizontal 15.75 kHz vertical 60 Hz
Scanning System	NTSC color 525 line 60 fields/second
Video Output Level	1.0 Vp-p 75 ohm
Video S/N Ratio	greater than 46 dB
Weight	10 oz
White Balance/Gain Control	Auto

Downloads

