



Color Miniature Weatherproof Camera with Removable Sunshield



VL-634

Features

The VL-634 is a great choice for fixed focus applications with its sleek look and miniature dimensions. The camera comes complete with protective sunshield, mount and features multiple mounting options.

Specifications

CCD	1/3" Inter Line Transfer CCD
Image Signal Process	Digital Signal Processing System
Number of Pixels	512 H x 492 V
Picture Elements	Approximately 270K
Horizontal Resolution	380 TV Lines
Sync System	Internal
Scanning System	2:1 Interlace
Sensitivity	1 LUX
S/N Ratio	48 dB
Auto Gain Control	YES
White Balance	YES
Back Light Compensation	AUTO
Electronic Shutter	AUTO: 1/60 Sec to 1/100,000 Sec
Video Output Signal	1 Volt p-p composite video output into 75 Ohms
Power Consumption	120 mA
Lens	3.6mm Lens, F1.6 standard
Operating Temperature	-20°F to 120°F
Mounting Hardware	Universal mounting bracket and installation tool included
Dimensions95"Diameter x 3.15"L
Weight	3 Oz.

Package Includes:

VL-634 Camera	Instructions
Warranty card	Installation Tool
Universal Mounting Bracket	

For more information contact us at:

Speco Technologies 200 New Highway, Amityville, NY 11701 Web: www.specotech.com
Toll Free: 1-800-645-5516 In Metro NY: 631-957-8700 Fax: 631-957-9142 or 631-957-3880

Specifications subject to change

VL-634