

## 20 Watt Talk-Back Mobile Amplifier

**PAT20TB** 20W mobile amplifier

### Features

- Talk-back feature turns a remote speaker (not included) into a listening device for two-way conversations
- Includes push to talk handheld “CB” style microphone (Replacement part# PAT20TBMIC)
- Includes mounting hardware
- 5 year warranty



### Specifications

|                          |   |
|--------------------------|---|
| RMS Output Power.....    | 12W                                     |
| Max. Output Power.....   | 22W                                     |
| AC Power Consumption.... | n/a                                     |
| Power Supply .....       | DC 11V to 16V                           |
| Zones.....               | 1                                       |
| Speaker Outputs.....     | 4/8 Ohms                                |
| Inputs.....              | 1 x Mic (1/4"), 1 x Aux (1/4")          |
| Frequency Response ..... | 50Hz ~ 20KHz (±3dB)                     |
| Tone Control .....       | Up to +10kHz                            |
| THD .....                | Less than 0.5% @1KHz                    |
| Signal/Noise Ratio.....  | Microphone: >65dB / Line: >70 dB        |
| Controls .....           | Volume for each source, Tone, Talk-back |
| Indicators .....         | Power                                   |
| Dimensions.....          | 5.1" (W) x 1.25" (H) x 4.5" (D)         |
| Weight .....             | 2 lbs.                                  |
| Includes .....           | Microphone                              |
| Listings .....           | CE, FCC, RoHS                           |

### Optional Accessory



**PAT20TBMIC**  
Replacement  
Microphone

Speco Technologies is constantly developing and improving products. We reserve the right to modify product design and specifications without notice and without incurring any obligation. Spec Rev. 10/28/14