

30 Watt P.A. Amplifier with 30 Preset Digital Tuner

P30FA 30W P.A. amplifier

Features

- Digital 30 station preset FM/AM tuner
- Telephone paging input and Music-on-hold output
- Mic1 selectable priority paging
- 4/8 Ohms or 70/25V output
- 5 year warranty



rear of unit

Specifications

RMS Output Power.....	30W
Max. Output Power.....	60W
AC Power Consumption ...	80W
Power Supply	AC 117V/220V, 50Hz/60Hz
Zones.....	1
Speaker Outputs.....	4/8/16 Ohms, 70/25V
Inputs.....	1 x Antenna (BNC), 1 x Aux (Stereo RCA), 2 x Mic (XLR), 1 x Mic (1/4"), 1 x TEL (terminal)
Frequency Response	30Hz ~ 20kHz (±3dB)
Tone Control	Bass ± 10dB, Treble ± 10dB
THD	Less than 1% @ 1kHz
Signal/Noise Ratio	Microphone: >60dB, Line: >80dB
Controls	Volume for each source, Master Volume, Tone, Tuner
Telephone	TEL in and MoH Out
Indicators	Tuner, power level
Dimensions.....	16.9" (W) x 3.5" (H) x 11.6" (D)
Weight	14 lbs.
Includes	Rack mount hardware, Antenna
Listings	CE, FCC, RoHS