

## Wired Microphones & Accessories

### HANDHELD DYNAMIC MICROPHONE

- Dynamic
- Uni-Directional
- 50Hz-16kHz
- 700-Ohms impedance
- Sensitivity: -54dB±3dB
- 3 Pin XLR Male Connector
- On/Off Switch
- 20 ft., XLR MIC Cable Included
- Carrying Case



**MCHH100**

### PROFESSIONAL CONDENSER MICROPHONE

- Back Electret Condenser
- Uni-directional
- Zinc-die Casting Housing
- Ideal for Clear Reproduction of Natural Sound
- 50Hz-18kHz
- 600-Ohms impedance
- Sensitivity:-45dB±3dB
- Max. Input SPL: 130dB (at 1kHz ≥1% T.H.D)
- S/N Ratio: ≥70dB
- Phantom Power Requirement: 9V-52V DC phantom or 1.5V Battery



**MCHH300**

### PROFESSIONAL GOOSENECK MICROPHONE

- Back Electret Condenser
- Uni-directional
- Blue LED On/Off Indicator
- Flexible Gooseneck
- Windscreen Sponge over MIC
- 50Hz-16kHz
- 1000-Ohms impedance
- Sensitivity: -45dB±3dB
- Three Wire Connection
- 9V-52V DC Phantom Power Required



**MCGN300**

### DYNAMIC GOOSENECK MICROPHONE WITH PUSH TO TALK SWITCH

- Unidirectional
- 16 1/4" gooseneck
- 500-Ohms low impedance
- Mounting base



**MGS1**

### PROFESSIONAL TABLETOP CONFERENCE MICROPHONE

- Back Electret Condenser
- Uni-directional
- Flexible Gooseneck
- Easy Touch On/Off Button
- Blue LED On/Off Indicator
- 50Hz-16kHz • 500-Ohms impedance
- Sensitivity: -37dB±3dB
- XLR 3 Pin Male Connector
- Two AA Batteries Included
- 20 ft., XLR MIC Cable Included
- 9V-52V DC Phantom or 1.5V Battery
- Windscreen Sponge over MIC



**MCDD300**

### GOOSENECK ADJUSTABLE TABLETOP MICROPHONE

- Momentary switch for priority paging, & lock down switch for continuous use
- 6" gooseneck extension and 5' cord
- Cannon 3 pin XLR male connector
- Impedance: low-600 Ohms high-50 kHz
- Sensitivity: High-53dB +/- 3dB Low 71 dB +/- 3 dB



**MHL5S**

### PROFESSIONAL HANGING MICROPHONE

- Back Electret Condenser
- Uni-directional
- Spring Neck Included
- 50Hz-16kHz
- 250-Ohms impedance
- Sensitivity: -37dB±3dB
- XLR 3 Pin Male Connector
- 9V-52V DC Phantom Power Required
- 20 ft. cable included



**MCHM300**

### PROFESSIONAL BOUNDARY MICROPHONE

- Back Electret Condenser
- Uni-directional
- Stealth Design
- 20 feet, XLR Cable Included
- 60Hz-16kHz
- 250-Ohms impedance
- Sensitivity: -36dB±3dB
- 9V-52V DC Phantom Power Required
- Mute Feature



**MCBM300**

### PUSH TO TALK HANDEHELD MICROPHONE

- 5 wire
- 500-Ohms impedance
- For CB & professional communications
- Push to talk
- Unbalanced (TS) plug



**DM520**  
1/4" phono plug **DM520P**



### PHANTOM POWER ADAPTERS FOR CONDENSER MICROPHONES

- 48V DC phantom power supply is designed for condenser microphones.
- Male XLR mic output connector • Female XLR mic input connector • 110/0V 60/50Hz
  - 5ft. AC power cord included

**MCPP100**