

VM10LCD

Features

- Professional TFT LCD for surveillance with multiple connections
- Picture-In-Picture feature that allows multi-picture display (in VGA mode)
- High brightness level and contrast ratio with super wide viewing angle
- Built-in 3D comb filter and 3D de-interlace for display picture performance
- Fast response time and refresh rate

Specifications

- Panel Size 10.4"
- Aspect Ratio 4:3
- Resolution/Scan..... 640 x 480
- Brightness 350 cd/m²
- Contract Ratio 300:1
- Viewing Angle (H/V) Left 70° / Right 70° / Up 40° / Down 70°
- Response Time 6ms (Typ.)
- Sync. Format NTSC / PAL
- Frequency (Horizontal) PC: 31.5K
- Frequency (Vertical) PC: 60Hz - 75Hz, Video: 50 / 60Hz
- Video Interface D-SUB 15IN x 1, Video In x 2 (BNC), Video Out x 2 (BNC), S-Video In x 1
- Audio Interface In x 2, Audio Out x 2, PC-Audio In x 1
- Input Power DC In x 1
- Termination 75 Ohm (AutoTermination)
- Built-In Speakers Yes (2pcs)
- Front Panel Button Power, Source, Up, Down, Menu, Auto
- OSD Language Multi Language
- VESA Mounting VESA 75mm x 75mm
- Power Supply 12VDC
- Power Consumption (max.) 17.2W
- Operating Temperature/
Humidity 14° F - 122° F / RH 20% - 80%
- Dimensions 10.3" (W) x 8.8" (H) x 2.5" (D)
- Weight (N.W. / G.W.) 4 lbs. / 6.4 lbs.
- Included in Package Power cord, user manual, remote control

