



[new products](#)

[corporate news](#)

[software downloads](#)

[how to use search](#)

[reference](#)

[home](#)

products



Designer Series B/W Weatherproof Bullet with Sunshield, White Housing (CVC-1700W)

With a sleek look and miniature dimensions, the CVC-1700 is a great choice for fixed focus applications. It is complete with a protective sunshield and features multiple mounting options. This B/W camera has a 1/3" CCD with a 420 line resolution. It also has low power consumption and low illumination at 0.02 lux. It uses a built-in electronic iris and electronic shutter with a 3.6mm lens. An adjustable mounting bracket, and a 12V DC power supply are included. This camera is also offered in a silver (CVC-1700S), black (CVC-1700BR) or bronze (CVC-1700BR) housing color, along with B/W versions that can be found under our 6700 series.

Technical Specifications

Dimensions	3.94"L x 1.54"W x 1.38"H
Electronic Shutter	1/60 - 1/100000 seconds
Housing Color	White
Humidity	within 95 % RH
Image Device	1/3" B/W CCD image sensor
Lens	3.6mm
Lens Option	Sold Separately available in 2.5, 6, 8, and 12mm
Minimum Illumination	0.02 lux
Number of Pixels	512 horizontal x 492 vertical
Operating Temperature	14 degrees F - 122 degrees F
Output	BNC connector
Power Consumption	100 mA
Power Supply	regulated 12V DC power supply (UL and CSA listed)
Resolution	420 line
Scanning Frequency	15.75 kHz horizontal 60 Hz vertical
Video Output	1.0 Vp-p 75 ohm
Video S/N Ratio	greater than 46 dB
Weight	5.8 oz

Downloads

