



[new products](#)

[corporate news](#)

[software downloads](#)

[how to use search](#)

[reference](#)

[home](#)

# products



## 3 B/W Cameras Housed In Vandal Resistant Dome (CVC-386TP3)

Our three housed 1/3" B/W CCD vandal resistant dome has three 3.6mm fixed lenses, an ultra high impact dome cover, and a heavy duty metal base. It is ideal for indoor, as well as covered outdoor environments. It features a 0.02 lux with 420 line resolution. A mount is included for ceiling placement.

### Technical Specifications

Dimensions	5"L x 5"W x 3.5"H
Electronic Shutter	auto 1/60 - 1/100,000 second per camera
Housing	black ultra high impact dome, vandal resistant
Humidity	Within 95 % RH
Image Device	(3) 1/3" B/W CCD image sensors
Lens	3.6mm per camera
Minimum Illumination	0.02 lux per camera
Number of Pixels	512 horizontal x 492 vertical per camera
Operating Temperature	14 degrees F - 122 degrees F
Output	Video - RCA with BNC adapter, power- DC jack per camera
Power Consumption	100 mA per camera
Power Supply	regulated 12V DC power supply included (UL and CSA listed) per camera
Resolution	420 lines per camera
Scanning System	EIA standard 525 line 60 fields/second per camera
Video Output Level	1.0 Vp-p 75 ohm per camera
Video S/N Ratio	Greater than 46 dB per camera

### Downloads

