



products



Color Vandal Resistant Varifocal Dome Camera (CVC-7405TP)

Our 1/4" color CCD vandal resistant dome has a 4-9mm varifocal lens, an ultra high impact dome cover, and a heavy duty metal base. It is ideal for indoor, as well as outdoor environments. It features a 1.0 lux with 350 line resolution. A mount is included for ceiling placement. A B/W version of this camera is available and can be found under model number CVC-3805TP. A fixed lens version of this camera is also available, and can be found under model numbers CVC-745P (Color) and CVC-385TP (B/W).

Technical Specifications

Dimensions	5"L x 5"W x 3.5"H
Electronic Shutter	auto 1/60 -1/100,000 seconds
Housing	vandal resistant, weatherproof, ultra high impact dome cover, heavy metal base, wall or ceiling mountable, black
Humidity	within 95 % RH
Image Device	1/4" color CCD image sensor
Lens	4-9mm varifocal dome
Minimum Illumination	1.0 lux
Number of Pixels	512 line horizontal x 492 vertical
Operating Temperature	14 degrees F - 122 degrees F
Output	Video- RCA with BNC adapter, power- DC jack
Power Supply	regulated 12V DC power supply included (UL and CSA listed)
Resolution	350 line
Scanning Frequency	horizontal 15.75 kHz vertical 60 Hz
Scanning System	NTSC color 525 line
Video Output Level	1.0 Vp-p 75 ohm
Video S/N Ratio	greater than 46 dB