# Reentrant Horn Loudspeaker

## Model IH8A



### Description

The Bogen Model IH8A is a double reentrant horn-type loudspeaker designed for paging applications.

Excellent intelligibility, handsome compact styling, and all metal, weatherproof construction make the model IH8A perfect for use indoors or outdoors with Bogen sound equipment.

A detachable mounting bracket, which includes a wing-nut locking device, provides precise positioning of the horn in the vertical and horizontal planes. The unit is finished in textured mocha enamel.

#### **Features**

- · High intelligibility and efficiency
- · Weatherproof, all metal construction
- 12" connecting cable for easy installation

# Architects &

The loudspeaker shall be a Bogen Model IH8A reentrant horn-type loudspeaker, or approved equivalent, providing a frequency response from 350Hz to 12kHz. Input impedance shall be 8 ohms. Rated power output shall be 15 watts. Dispersion shall be 130°. Sound pressure level, measured four feet on axis at rated output, shall be at least 120dB.

# Engineers Specifications

The loudspeaker shall be of weatherproof, all metal construction, with driver enclosed within a waterproof housing. A 12-inch connecting cable shall be provided.

An all-purpose mounting bracket shall provide precise positioning in the vertical and horizontal planes. Bracket and loudspeaker shall be finished in textured mocha enamel. The unit shall measure 6-1/4" dia.  $\times$  6"D. The product weight shall be 2-1/2 lbs.

### **Specifications**

Power Rating: 15 watts

Frequency Response: 350Hz to 12kHz

**Input Impedance:** 8 ohms

**Dispersion:** 130°

**Sound Pressure Level:** 120dB @ 4 feet on axis with

15-watt input at 1000Hz

**Dimensions:** 6-1/4" diameter bell x 6"D

**Product Weight:** 2-1/2 lbs.

