

Economizer



This high quality, low cost cabinet rack is available with 19" panel width in both ventilated and non-ventilated versions.

Design Features

Welded Frame: 14-gauge steel vertical rails. 16-gauge steel top and bottom. Uniquely designed, 16-gauge steel rail supports. Furnished complete with removable sides, rear door and one pair of panel mounting rails.

Panel Mounting Rails: 12-gauge steel. Fully adjustable, tapped #10-32 in front on E.I.A. universal spacing. (Use #7346 screws - order separately) Separate .28 diameter holes provided for mounting accessories.

Side Panel: 20-gauge steel. Removable from outside for easy access.

Bottom: Pierced for RC-7758 casters, and with one 9.56 square hole and four 1.11 knock outs for cable access.

1200# Equipment load capacity.

Bonus Features

Finishes

Sand Texture (S), Royal Blue Texture (RB), and Black Texture (BT) are standard.

Available in other Bud textured finishes at no extra cost.

Economizer Racks with 19" Panel Width											
Non-Ventilated			Ventilated			Panel	Outside	Outside	Outside	Clear	
Catalog Number	Acce- ssories	Drawings	Catalog Number	Acce- ssories	Drawings	Space	Height A	Width B	Depth C	Inside Depth D	Weight (Lbs.)
ER-16502			ER-16602			42.00"	47.31"	22.00"	18.50"	17.00"	110
ER-16503			ER-16603			52.50"	57.81"	22.00"	18.50"	17.00"	124
ER-16504			ER-16604			61.25"	66.56"	22.00"	18.50"	17.00"	139

ER-16505	ER-16605			70.00"	75.31"	22.00"	18.50"	17.00"	151
ER-16506	ER-16606			78.75"	84.06"	22.00"	18.50"	17.00"	163
ER-16511	N/A	N/A	N/A	21.00"	25.31"	22.00"	25.50"	24.00"	94
ER-16512	ER-16612			42.00"	47.31"	22.00"	25.50"	24.00"	128
ER-16513	ER-16613			52.50"	57.81"	22.00"	25.50"	24.00"	145
ER-16514	ER-16614			61.25"	66.56"	22.00"	25.50"	24.00"	162
ER-16515	ER-16615			70.00"	75.31"	22.00"	25.50"	24.00"	175
ER-16516	ER-16616			78.75"	84.06"	22.00"	25.50"	24.00"	189
ER-16521	N/A	N/A		21.00"	25.31"	22.00"	30.75"	29.25"	109
ER-16522	ER-16622			42.00"	47.31"	22.00"	30.75"	29.25"	143
ER-16523	ER-16623			52.50"	57.81"	22.00"	30.75"	29.25"	160
ER-16524	ER-16624			61.25"	66.56"	22.00"	30.75"	29.25"	180
ER-16525	ER-16625			70.00"	75.31"	22.00"	30.75"	29.25"	194
ER-16526	ER-16626			78.75"	84.06"	22.00"	30.75"	29.25"	209



