



## BudRack Professional Series






## Design Features


- Sturdy and durable steel construction Mounting rails 14 GA, other parts 18 GA.
- Finished complete with ventilated tempered glass front door, locking rear door, removable sides
- EIA 310 Compliant for 19" rack-mount equipment
- Two pairs of fully adjustable panel mounting rails included. The panel mounting rails include unique notch at each "U" point to allow for rapid equipment location identification
- Top mount fan box installed. Two fans for 23" depth, four fans for 31" depth
- Includes ventilated shelves (one shelf in the 24U high cabinet, two shelves in the 40U and 45U cabinets)
- Includes Installed Casters
- Large cutout in base. Cutout comes covered by 2.5" deep metal cover plates that allow for adjustable opening providing as much or as little open space for cable access
- Two (2) additional 13" x 2.5" cutouts in front and rear of base also come with readily removable covers
- Vented at top and bottom of sides, which also can be locked

- Comes fully assembled in a wooden crate to eliminate freight damage
- Finish: Black textured powder coating easy to clean.
- Other sizes and modifications are available upon request.

BudRack Professional Series													
			Space hes)		Overall Dimensions (inches)			Clear Inside Depth	Weight				
Catalog No.	Drawings	Width	Height	"U"	Width	Depth	Height	(inches)	(Lbs.)				
BRP-12202		19.00	42.00	24	23.62	23.62	49.40	20.88	222				
BRP-12206		19.00	70.00	40	23.62	23.62	77.40	20.88	305				
BRP-12208		19.00	78.75	45	23.62	23.62	86.15	20.88	327				
BRP-12212		19.00	42.00	24	23.62	31.50	49.40	28.75	254				
BRP-12216		19.00	70.00	40	23.62	31.50	77.40	28.75	345				
BRP-12218		19.00	78.75	45	23.62	31.50	86.15	28.75	370				







MATERIAL: PANEL MOUNTING RAILS - 14 GA. (0.08" [2.0] THK.) STEEL ALL OTHER PARTS - 18 GA. (0.05" [1.2] THK.) STEEL

FINISH:

BLACK TEXTURED POWDER COATING


PANEL MOUNTING RAILS HAVE 0.35" [8.9] SQUARE HOLES ON E.I.A. UNIVERSAL HOLE SPACING


SUPPLIED HARDWARE KIT TO INCLUDE:

QTY. (25) M6 CAGE NUT QTY. (25) M6 PAN HEAD SCREW

QTY. (25) NYLON FLAT WASHER QTY. (4) M10  $\times$  2.25" [57.2] LG. STEM LEVELER W/HEX NUT

QTY. (8) KEYS





TOLERANCE ALL DIMENSIONS: ±0.08" [2.0]

	ITEM REQ'D. PART		T N□.		DESCRIPTION	
TOLERANCES:	MAT:	AS NOTED	SCALE:		NAME:	
±.005 BETWEEN HOLE CENTERS	FINISH: AS NOTED		BID		24U BUDRACK	
±.015 FRDM SHEARED EDGE   ±.032 FRDM A BENT SURFACE	DR. DAB	6-20-08			PROFESSIONAL SERIES	
±.063 BETWEEN ASSEMBLED	CH.		BUD INDUS	, i	IC.	
QTY. USED ON UNLESS OTHERWISE SPECIFIED	APP.		WILLOUGHBY, OHIO		DWG. N□.	BRP-12212