



Design Features

- *All welded 14 gauge steel frame with "U" shaped 16 gauge steel panel mounting rail supports.
- *Door, 20 gauge steel. Sides and top, 18 gauge steel.
- *Adjustable front and rear panel mounting rails tapped #10-32 on E.I.A. universal spacing. (use #7346 screws order separately)
- *Accommodates 19" wide E.I.A. panels.
- *Bottom pierced for RC-7758 casters. *1.109 inch diameter knockout holes in base.
- *1200# equipment load capacity.

Bonus Features

- *Interiors are accessible from front and rear for easy installation and maintenance of components.
- *One door furnished. May be used on front or rear.
- *Add-A-Rack System used to combine two or more enclosures into one integral system.
- *Shipped completely assembled.

Finishes

Grey Texture (GT), Royal Blue Texture (RB). Available in other Bud textured finishes at no extra cost.

SERIES 60 Cabinet Rack (19" Panel Width)											
Catalog No.	Acce- ssories	Drawings	Panel Space (PS)			Outside Depth (C)		Weight (Lbs.)			
60-2300			21.00"	29.62"	24.06"	22.00"	20.50"	112			
60-2301			31.50"	40.12"	24.06"	22.00"	20.50"	137			
60-2302			42.00"	50.62"	24.06"	22.00"	20.50"	162			

60-2303	52.50"	61.12"	24.06"	22.00"	20.50"	189
60-2304	61.25"	69.87"	24.06"	22.00"	20.50"	215
60-2305	70.00"	78.62"	24.06"	22.00"	20.50"	227
60-2306	78.75"	87.37"	24.06"	22.00"	20.50"	244
60-2307	21.00"	29.62"	24.06"	25.50"	24.00"	123
60-2308	31.50"	40.12"	24.06"	25.50"	24.00"	145
60-2309	42.00"	50.62"	24.06"	25.50"	24.00"	170
60-2310	52.50"	61.12"	24.06"	25.50"	24.00"	202
60-2311	61.25"	69.87"	24.06"	25.50"	24.00"	216
60-2312	70.00"	78.62"	24.06"	25.50"	24.00"	231
60-2313	78.75"	87.37"	24.06"	25.50"	24.00"	263
30-2300	21.00"	29.62"	24.06"	30.75"	29.25"	154
30-2301	31.50"	40.12"	24.06"	30.75"	29.25"	174
30-2302	42.00"	50.62"	24.06"	30.75"	29.25"	202
30-2303	52.50"	61.12"	24.06"	30.75"	29.25"	225
30-2304	61.25"	69.87"	24.06"	30.75"	29.25"	245
30-2305	70.00"	78.62"	24.06"	30.75"	29.25"	268
30-2306	78.75"	87.37"	24.06"	30.75"	29.25"	294

