


Accessories - Shelves

Ventilated Sliding Shelves




Design Features

Sliding shelves come in widths that either fit 19" or 24" wide panel spaces and all cabinet rack depths. Shelves are 16gauge steel and flanged on all four sides for added support. Universal mounting brackets allow flexibility in mounting. Shelves allow sufficient room in rear for cables and power outlet strips. Requires two pairs of panel mounting rails per cabinet rack. Also Available in a Non-Ventilated version.

| Sliding Shelves Ventilated | | | | | | | | | |
|----------------------------|--|--------|----------------------------|--------|--------|------------------|--------|-------------|--|
| Catalog Number | | | Max. Clear Inside Depth | | Depth | Load Rating Lbs. | Travel | Weight Lbs. | |
| SH- 2391 | | 19.00" | 17.00" | 17.00" | 14.25" | 140 | 8.00" | 8.75 | |
| SH- 2392 | | 19.00" | 20.50" | 17.00" | 17.75" | 120 | 12.00" | 9.75 | |
| SH- 2393 | | 19.00" | 24.00" | 17.00" | 21.25" | 92 | 15.00" | 12 | |

| SH-2394 | 19.00" | 29.25" | 17.00" | 26.50" | 70 | 19.00" | 13.5 |
|---------|--------|--------|--------|--------|-----|--------|-------|
| SH-2491 | 24.00" | 17.00" | 22.00" | 14.25" | 140 | 8.00" | 10 |
| SH-2492 | 24.00" | 20.50" | 22.00" | 17.75" | 120 | 12.00" | 11.5 |
| SH-2493 | 24.00" | 24.00" | 22.00" | 21.25" | 92 | 15.00" | 14 |
| SH-2494 | 24.00" | 29.25" | 22.00" | 26.50" | 70 | 19.00" | 15.75 |





| PART N□. | | SHELF | | SLIDE | | | | | | | | |
|-----------|---------|-------|--------|--------|--------|--------|--------|----|--------|----|--------|-----|
| I AKT NU. | | SHELL | | LENGTH | TRAVEL | LOAD | E | F | G | H | I | J |
| PLAIN | VENTED | Α | В | С | D | RATING | | | | | | |
| SH-2387 | SH-2391 | 17 | 14.250 | 12 | 9 | 140 | 17.875 | 8 | 12.000 | 29 | 14.500 | 270 |
| SH-5388 | SH-2392 | | 17.750 | 16 | 12 | 120 | | 10 | 15.000 | | | 330 |
| SH-2389 | SH-2393 | | 21.250 | 20 | 15 | 92 | | 12 | 18,000 | | | 390 |
| SH-2390 | SH-2394 | 17 | 26.500 | 26 | 19 | 70 | 17.875 | 16 | 24.000 | 29 | 14.500 | 510 |
| SH-2487 | SH-2491 | 22 | 14.250 | 12 | 9 | 140 | 22.875 | 8 | 12.000 | 41 | 20.500 | 378 |
| SH-2488 | SH-2492 | | 17.750 | 16 | 12 | 120 | | 10 | 15,000 | | | 462 |
| SH-2489 | SH-2493 | | 21.250 | 20 | 15 | 92 | | 12 | 18.000 | | | 546 |
| SH-2490 | SH-2494 | 55 | 26,500 | 26 | 19 | 70 | 22.875 | 16 | 24.000 | 41 | 20.500 | 714 |