



Design Features

- *Anodized aluminum extrusion top trim.
- *All welded 14 gauge steel frame with "U" shaped 16 gauge steel panel mounting rail supports.
- *Door, 20 gauge steel.

Sides and top, 18 gauge steel.

- *Adjustable front and rear panel mounting rails tapped #10-32 on E.I.A. universal spacing. (use #7346 screws order separately)
- *Accommodates 19" wide E.I.A. panels.
- *Bottom pierced for RC-7758 casters.
- *1.109 inch diameter knockout holes in base.
- *1200# equipment load capacity.

Bonus Features

- *Interiors are accessible from front and rear for easy installation and maintenance of components.
- *Readily removable rear door.
- *Shipped completely assembled.

Finishes

Grey Texture (GT), Royal Blue Texture (RB). Available in other Bud textured finishes at no extra cost.

SERIES 2000 Cabinet Racks (19" Panel Width)											
Non-Ventilated			Ventilated						Outside		
Catalog No.	Acce- ssories	Drawings	Catalog No.	Acce- ssories	Drawings	Space (PS)	Height (A)	Width (B)	Depth (C)	Inside Depth (D)	(Lbs.)
E-2000			N/A	N/A	N/A	21.00"	30.25"	24.19"	23.87"	20.50"	119

E-2003	N/A	N/A	N/A	42.00"	51.25"	24.19"	23.87"	20.50"	168
E-2004	N/A	N/A	N/A	52.50"	61.75"	24.19"	23.87"	20.50"	195
E-2005	N/A	N/A	N/A	61.25"	70.50"	24.19"	23.87"	20.50"	216
E-2006	N/A	N/A	N/A	70.00"	79.25"	24.19"	23.87"	20.50"	233
E-2007	N/A	N/A	N/A	78.75"	88.00"	24.19"	23.87"	20.50"	260
E-2008	E-2024			21.00"	30.25"	24.19"	27.37"	24.00"	129
E-2011	E-2027			42.00"	51.25"	24.19"	27.37"	24.00"	179
E-2012	E-2028			52.50"	61.75"	24.19"	27.37"	24.00"	215
E-2013	E-2029			61.25"	70.50"	24.19"	27.37"	24.00"	234
E-2014	E-2030			70.00"	79.25"	24.19"	27.37"	24.00"	244
E-2015	E-2031			78.75"	88.00"	24.19"	27.37"	24.00"	268
E30-2000	N/A	N/A	N/A	21.00"	30.25"	24.19"	32.62"	29.25"	150
E30-2003	N/A	N/A	N/A	42.00"	51.25"	24.19"	32.62"	29.25"	217
E30-2004	N/A	N/A	N/A	52.50"	61.75"	24.19"	32.62"	29.25"	248
E30-2005	N/A	N/A	N/A	61.25"	70.50"	24.19"	32.62"	29.25"	259
E30-2006	N/A	N/A	N/A	70.00"	79.25"	24.19"	32.62"	29.25"	303
E30-2007	N/A	N/A	N/A	78.75"	88.00"	24.19"	32.62"	29.25"	307



