

364W10K

([Home](#) : [Products](#) : [Sensors](#) : [Trimmers](#) : 364)



364 Series Trimmer, 10 kOhm, 0.5 W, 25 Turns, Square Body, Vertical Shaft

Actual product appearance may vary.

Product Specifications

Product Type	Trimmer
Watts	0.5 W
Turns	25
Element Type	Cermet
Resistance Value	10 kOhm
Resistance Tolerance	± 10 %
Temperature Coefficient	± 100 ppm/ °C
Body	9,53 mm [0.375 in] square
Shaft Location	Vertical
Rotational Life	200 cycles
Series Name	364
Availability	Global
UNSPSC Code	32121616
UNSPSC Commodity	32121616 Trimmer resistor