


PRODUCT SELECTION CHART

Switch & Potentiometer Boots : Full Pushbutton Boots - IP66/68 Rated (Fig 9)



## Full Pushbutton Boots - IP66/68 Rated

Thread Size	Max. Plunger Height		А		B O.D.		C I.D.		Military Part	APM Boot Part Number	Color*	HEXSEAL	E-SEEL
	inch	mm	inch	mm	inch	mm	inch	mm	Number	Fart Number		포	ŵ
<sup>3</sup> /8-27NS-2B	.330	8.38	.609	15.48	.641	16.27	.320	8.11	_	1221/12	Gray	•	
15/32-32NS-2B	.400	10.14	.719	18.26	.766	19.45	.375	9.53	_	1221/15	Gray	•	
<sup>3</sup> /8-24NF-2B	.330	8.38	.609	15.48	.641	16.27	.320	8.11	_	C1221/22	Clear		•
<sup>3</sup> /8-27NS-2B	.330	8.38	.609	15.48	.641	16.27	.320	8.11	_	C1221/21	Black		•
<sup>3</sup> /8-27NS-2B	.330	8.38	.609	15.48	.641	16.27	.320	8.11	_	C1221/21 4	Clear		•
3/8-32NEF-2B	.330	8.38	.609	15.48	.641	16.27	.320	8.11	_	C1221/23	Clear		•

Mounting nut material: Aluminum

\*Other colors available. Please consult factory.

:: close window ::