

## 1520230-2 Product Details

[Share](#) [Print](#) [Email](#)

No Image Available

**1520230-2**  
(7402K4)

TE Internal Number:  
1520230-2

 Active

### Power Toggle Switches

 Always EU RoHS/ELV Compliant (Statement of Compliance)

### Product Highlights:

- Double Pole - Single Throw Configuration (Pole-Throw)
- Toggle Length = 20.65 mm
- Toggle Style = Baton
- Bushing Length = 11.91 mm
- Termination Type = Screw-In Terminal

[View all Features](#)

### Quick Links

- ▶ [Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#)

[Request Sample](#)

[Find Similar Products](#)

[Buy Product](#)

## Documentation & Additional Information

### Product Drawings:

- [Customer Drawing](#) (PDF, English)

### Catalog Pages/Data Sheets:

- None Available

### Product Specifications:

- None Available

### Application Specifications:

- None Available

### Instruction Sheets:

- None Available

### CAD Files:

- None Available

[List all Documents](#)

### Related Products:

- [Tooling](#)

## Product Features (Please use the Product Drawing for all design activity)

### Product Type Features:

- Termination Type = Screw-In Terminal

### Electrical Characteristics:

- UL/CSA 250V Current Rating (A) = 20
- UL/CSA 125V Horse Power Rating (hp) = 1.50
- UL/CSA 250V Horse Power Rating (hp) = 2.00

### Dimensions:

- Bushing Length (mm [in]) = 11.91 [0.469]

### Housing Features:

- Toggle Length (mm [in]) = 20.65 [0.813]
- Toggle Style = Baton

### Configuration Features:

- Configuration (Pole-Throw) = Double Pole - Single Throw

### Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

### Other:

- Brand = Alcoswitch