

# **DANTONA**

**INDUSTRIES, INC.**

**For all your battery needs!**

## Power Tool Replacement Batteries



## **DANTONA PART SEARCH**



**Dantona Part # LAP-565LI-111**

**Voltage: 11.1**  
**Capacity: 4600**  
**Composition: LION**  
**Dimensions:**  
**Connector:**  
**Description:**

# DANTONA

INDUSTRIES, INC.




For all your battery needs!




## Power Tool Replacement Batteries



## DANTONA CATALOG

### DELL

	Part #	Volts	mAh	Type	X-Ref	
	6-1/3AASK-U	7.2	110	NiCd	DELL: 212N, 320N, 42873	
	COMP-10	** NO **	** LONGER **	** AVAILABLE **	DELL: 286AT, 300, 310, 316, 325, 386, SYSTEM 200	
	COMP-9	7.2	1900	Lithium	DELL: SYSTEM 200/286	

	LAP-563LI-148	14.8	2300	LION	DELL: 312-0365, 312-0366, 312-0416, HD438, HJ481, HJ483, HJ617, INSPIRON 1300, INSPIRON B120, INSPIRON B130, KD186, LATITUDE 120L, MJ131, MJ145, MJ472, TD429, TD611, TD612, UD384, UD532, UD533, WD414, WD415, WD416, WD417, XD184, XD185, XD187, YD120, YD131
	LAP-565LI-111	11.1	4600	LION	DELL: OGD775, OGD787, OJD605, OJD606, OJD610, OJD616, OJD634, OKD489, OKD491, OKD494, OKD495, OKD685, ORD300, ORD301, OTC030, OTD116, OTD117, OTD175, OTG226, OUD088, OUG260, 312-0383, 312-0384, 312-0386, GD775, GD787, JD606, JD610, JD616, JD634, JD648, KD489, KD491, KD494, KD495, LATITUDE D620 SERIES, PD685, RD300, RD301, TC030, TD116, TD117, TD175, TD226, UD088, UG260
	LAP-565LI-111-85	11.1	7800mAh / 85 Wh	LION	DELL: OGD775, OGD787, OJD605, OJD606, OJD610, OJD616, OJD634, OKD489, OKD491, OKD494, OKD495, OKD685, ORD300, ORD301, OTC030, OTD116, OTD117, OTD175, OTG226, OUD088, OUG260, 312-0383, 312-0384, 312-0386, GD775, GD787, JD606, JD610, JD616, JD634, JD648, KD489, KD491, KD494, KD495, LATITUDE D620 SERIES, PD685, RD300, RD301, TC030, TD116, TD117, TD175, TD226, UD088, UG260