

TOOLS

TEST AND MEASUREMENT TOOLS



Test and Measurement Tools

Retail Part No.	Bulk Part No.	Figure No.	Description	Features
12-5705		1	Tone Test Set	1000 Hz or 500/1000 Alt. Tone, Checks for Shorts, Locates Broken Cables in Walls
12-5706		2	Stationman Probe	Quickly and Easily Locates the Proper Cable Pair Containing the Tone Signal
12-105		3	Continuity Tester	42" Alligator Clip for Ground Connections
20-109		4	Resistance Decade (12-109)	Range from 1 Ohm to 11,111,110 Ohms in 1 Ohm Increments
12-1640		5	Sub-miniature I.C. Test Clips	Clips to Wires/Posts Up to .030" Diameter, 5/32" Travel, Rated: 500V AC/DC
12-1642		6	Miniature I.C. Test Clips	Clips to Wires Up to #16 Wire, 1/8" Travel, Rated: 1500V AC 1 Minute
12-1650		7	"Jumper" Wire Test Leads	27 AWG, 2 Each, 15" Long Thin Leads with Mini Clips, 10 Jumpers
12-1655		7	"Jumper" Wire Test Leads	21 AWG, Heavy Duty Leads, 1 Each, 22" Long Leads with Standard Size Clips, 5 Jumpers
12-1656		8	Heavy Duty Test Leads	Phone Tips to Banana Plugs 35" Leads 25 Ga. (20 x 38)
5101		9	Test Light	Tests Both AC & DC Circuits (80V AC to 500V AC or DC)
5120		10	High-Voltage Testing Screwdriver	Screwdriver/Tester Checks AC Voltage from 100 to 500V
5128		11	Automotive Electrical Tester	Tests "Hot" Leads in Vehicle Electrical Systems, Equipped w/18" Alligator Clip/Banana Plug Ends
12-1716		12	6" Stainless Steel Rule	15/32" Wide, Graduations in 32nds and 64ths, Decimal Equivalents on Back