



GREENLEE.
A Textron Company

MADE FOR THE TRADE!™

PUNCH UNT (7211-E-BB) 20.4MM (3/8"D/S)

Slug-Buster Knockout Punches 0.492 to 2.520



Image
Unavailable

Cat No: 7211EBB-20.4

UPC No: 783310319917

Description

- The contractor's choice - worldwide
- Unique punch profile also splits slugs for easier slug removal
- Use with battery-powered, hydraulic, ratchet or manual drivers
- Uses standard Greenlee dies and draw studs
- Slug Buster punches available in sizes up thru 2.52 IN (64.0 mm)
- U.S. Patent #4,543,722 for Slug-Buster

Specifications

- Application : For Punch Mild Steel, Aluminum, Fiberglass And Plastic
- Capacity Mild Steel : 14 GA (2.000 MM)
- Includes : Punch, Die And Draw Stud
- ISO : 20
- PG : 13
- Replacement Part : 31971 UPC 31971 Punch, 32004 UPC 32004 Die And 00042 00042 UPC Draw Stud
- Size : 0.803 IN (20.400 MM)
- Sub Brand : Slug-Buster
- Type : Knockout
- Weight : 0.300 LB (137.000 GM)