



The PowerMod® connector family offers minimum size and high power. The high performance contacts and insulator are rated for 30 amps continuous. Applications requiring lower operating temperatures can be de-rated using our current-temperature chart.

The one row female PowerMod connectors are offered in 3, 4, 6 and 8 circuit sizes. The connectors are available with straight crimp, straight PCB or right angle PCB contacts.

APP connectors are manufactured using the finest materials and world-class manufacturing processes. They embody the highest quality in the industry and meet all applicable industry standards.

FEATURES

- High performance contacts Rated to 30 amps per IEC 512-3
- Mechanically polarized housings Only mate one-way, ensuring proper mating
- High reliability positive retention latches

Are made from stainless steel to provide optimum performance

• PCB, panel or cable mounting

A wide variety of contact styles with optional mounting brackets, panel clips and back-shell hoods provide broad design flexibility



SPECIFICATIONS

Electrical		Mechanical	
Current Rating		Mating Cycles No Load per IEC 512-5	1,000
IEC 512-3, UL 1977 (Amperes)	30	Mating / Unmating Force per IEC 512-13	10 oz (3N) avg.
UL / CSA Voltage Rating (AC/DC)	600	Contact Retention per IEC 512-8	18 lb (80N) Crimp
Creepage / Clearance Distance	3.2 mm (.125") Min		9 lb (40N) PCB Connector
Contact Resistance per IEC 512-2	3 milliohms	Materials	
Dielectric Withstanding Voltage (AC)	2,200	Insulator	PPS UL94 V-0, material group IIIa
Contact Wire Range (AWG)	#24 to #12	Socket Body	Copper alloy, 200 μ inch Sn Bright over Ni
(mm²) *	0.25 to 4.0	Socket Contact	BeCu, 30 μ inch Au over Ni
Operating Temperature (°C)	-55° to 180°	Retention Clips	Stainless steel
(°F)	-67° to 356°	Hoods	PBT UL94 V-0
		POHS US File No. E26226 * Stra	anding, IEC class 5 or lower

ORDERING INFORMATION


PowerMod Part Number Plan - One Row Female							Tooling)				
Series	Rows	# Poles	Gender	Contact	Latch	Mounting	Custom	zed Cor	nnector	Part		
PM	4	0.3	Г	ВА	- 1	СН	- X	Х	X	Number	Mil-Standard	Description
PIVI	ı	0.3	Г	DA	L	Сп	- ^	^	^	TM0001	M22520/1-01	AF8 hand tool
1							Consult fa	ctory fo	r options	TP0001	N/A	WA27F pneumatic crimp tool
						OO - None				Turret & Lo	cator for TM000	1 & TP0001
03, 04, 06	6, 08 Poles					SB - R/A PCB	Snap Bracke	t		TL0001	N/A	For pin contacts
						HB - R/A PCB	Bracket with	Hole		TL0002	N/A	For socket contacts
F - Femal	е					ST - Self-tappi	ing screws fo	r straigh	t PCB mount	TL0004	M22520/1-03	For pin & socket contacts
00 N	. (0::			6 - L A		SP - Push in fa	astener for st	raight Po	CB mount			
	· ·	ntacts ordere		,	PC - Panel Clip				PM1000G1 N/A	Pneumatic four indent hand		
		older Standa										tool with locator
KA - K/A	RA - R/A PCB Solder Standard Length-RoHS			10		MC - Mounting Clip				Semi automatic loose piece		
						SC - Screw for	r 1.6mm pane	el mount	İ	DM40000	N1/A	crimp machine
										PM1002G1		Contact insertion tool
				L - Con	nector with latch ((standard for	contact	type OO)	PM1003G1	N/A	Contact extraction tool	
				O - No I	O - No latch							
					O - No I	atch						


www.andersonpower.com



One Row Cable Connector (female)

TEMPERATURE CHARTS






DIMENSIONS - mm(in.)

Cable Connector

ROWS CONTACTS	-/- mm	۱- in.
1 - 03	28.5	1.12
1 - 04	33.5	1.32
1 - 06	43.5	1.71
1 - 08	53.5	2.11



See accessory section for panel clip and mounting clip cut-out dimensions.

ORDERING INFORMATION

Cable Connector

Part	
Number Description	
PM103FOOLOO 1x3 FEMALE Cable Connec	ctor
PM104FOOLOO 1x4 FEMALE Cable Connec	ctor
PM106FOOLOO 1x6 FEMALE Cable Connec	ctor
PM108FOOLOO 1x8 FEMALE Cable Connec	ctor

Panel Mount With Mounting Clip

Description
1x3 FEMALE Cable Connector
1x4 FEMALE Cable Connector
1x6 FEMALE Cable Connector
1x8 FEMALE Cable Connector

With Clam Shell Hood & Strain Relief

Part	
Number	Description
PM103FOOLCH	1x3 FEMALE Cable Connector
PM104FOOLCH	1x4 FEMALE Cable Connector
PM106FOOLCH	1x6 FEMALE Cable Connector
PM108FOOLCH	1x8 FEMALE Cable Connector

Panel Mount With Screws

Part	
Number	Description
PM103FOOLSC	1x3 FEMALE Cable Connector
PM104FOOLSC	1x4 FEMALE Cable Connector
PM106FOOLSC	1x6 FEMALE Cable Connector
PM108FOOLSC	1x8 FEMALE Cable Connector

With Snap-in Panel Clip

Part	
Number	Description
PM103FOOLPC	1x3 FEMALE Cable Connector
PM104FOOLPC	1x4 FEMALE Cable Connector
PM106FOOLPC	1x6 FEMALE Cable Connector
PM108FOOLPC	1x8 FEMALE Cable Connector

Crimp Contacts

Part	Wire					
Number	Description	AWG	sq. mm			
PM16S2024S32	Socket	#24 / 20	0.50 / 0.75			
PM16S1620S32	Socket	#20 / 16	0.50 / 1.5			
PM16S1416S32	Socket	#16 / 14	1.5 / 2.5			
PM16S12S32	Socket	#12	2.5 / 4.0			





One Row Right Angle PCB (female)


DIMENSIONS - mm(in.)

1 Row - PCB Right Angle Connector










1 Row - PCB Hole Layout For Right Angle Connector

ROWS	А		L	1	L2	
CONTACTS	mm	in.	mm	in.	mm	in.
1 - 03	28.5	1.12	10	0.39	22.3	0.88
1 - 04	33.5	1.32	15	0.59	27.3	1.07
1 - 06	43.5	1.71	25	0.98	37.3	1.47
1 - 08	53.5	2.11	35	1.38	47.3	1.86



ORDERING INFORMATION

With Latch

F	t

Number	Description	
PM103FRALOO	1x3 FEMALE Right Angle PCB Solo	der
PM104FRALOO	1x4 FEMALE Right Angle PCB Solo	der
PM106FRALOO	1x6 FEMALE Right Angle PCB Solo	der
PM108FRALOO	1x8 FEMALE Right Angle PCB Solo	der

Snap Bracket & Latch

Part

Number	Description	
PM103FRALSB	1x3 FEMALE	Right Angle PCB Solder
PM104FRALSB	1x4 FEMALE	Right Angle PCB Solder
PM106FRALSB	1x6 FEMALE	Right Angle PCB Solder
PM108FRALSB	1x8 FEMALE	Right Angle PCB Solder

Bracket With Hole & Latch

Part

Number	Description	
PM103FRALHB	1x3 FEMALE	Right Angle PCB Solder
PM104FRALHB	1x4 FEMALE	Right Angle PCB Solder
PM106FRALHB	1x6 FEMALE	Right Angle PCB Solder
PM108FRALHB	1x8 FEMALE	Right Angle PCB Solder

No Latch

- 1	D,	٠,	4
	Г.	11	ι

Number	Description	
PM103FRAOOO	1x3 FEMALE	Right Angle PCB Solder
PM104FRAOOO	1x4 FEMALE	Right Angle PCB Solder
PM106FRAOOO	1x6 FEMALE	Right Angle PCB Solder
PM108FRAOOO	1x8 FEMALE	Right Angle PCB Solder

Snap Bracket & No Latch

Part

Number	Description	
PM103FRAOSB	1x3 FEMALE Right Angle PCB Solder	
PM104FRAOSB	1x4 FEMALE Right Angle PCB Solder	
PM106FRAOSB	1x6 FEMALE Right Angle PCB Solder	
PM108FRAOSB	1x8 FEMALE Right Angle PCB Solder	

Bracket With Hole & No Latch

Part

Number	Description
PM103FRAOHB	1x3 FEMALE Right Angle PCB Solder
PM104FRAOHB	1x4 FEMALE Right Angle PCB Solder
PM106FRAOHB	1x6 FEMALE Right Angle PCB Solder
PM108FRAOHB	1x8 FEMALE Right Angle PCB Solder


PCB contacts and mounting accessories are designed for a board thickness of 1.60mm (.063) with a contact protrusion of 2.10 (.083). Other contact lengths are available upon request.





One Row Straight PCB (female)

DIMENSIONS - mm(in.)

1 Row - PCB Straight Solder Connector










1 Row - PCB Hole Layout For Straight Solder Connector

ROWS	Α		L1		L2	
CONTACTS	mm	in.	mm	in.	mm	in.
1 - 03	28.5	1.12	10	0.39	22.3	0.88
1 - 04	33.5	1.32	15	0.59	27.3	1.07
1 - 06	43.5	1.71	25	0.98	37.3	1.47
1 - 08	53.5	2.11	35	1.38	47.3	1.86



ORDERING INFORMATION

With Latch

Part		
Number	Description	
PM103FBALOO	1x3 FEMALE	Straight PCB Solder
PM104FBALOO	1x4 FEMALE	Straight PCB Solder
PM106FBALOO	1x6 FEMALE	Straight PCB Solder
DM108ERALOO	1v8 FFMALE	Straight PCR Solder

Push On PCB Fastener & Latch

Part	
Number	Description
PM103FBALSP	1x3 FEMALE Straight PCB Solder
PM104FBALSP	1x4 FEMALE Straight PCB Solder
PM106FBALSP	1x6 FEMALE Straight PCB Solder
PM108FBALSP	1x8 FEMALE Straight PCB Solder

Self-tapping Screws For PCB Mount & Latch

Part	
Number	Description
PM103FBALST	1x3 FEMALE Straight PCB Solder
PM104FBALST	1x4 FEMALE Straight PCB Solder
PM106FBALST	1x6 FEMALE Straight PCB Solder
PM108FBALST	1x8 FEMALE Straight PCB Solder

All Data Subject To Change Without Notice

PCB contacts and mounting accessories are designed for a board thickness of 1.60mm (.063) with a contact protrusion of 2.10 (.083). Other contact lengths are available upon request.

No Latch

Description
1x3 FEMALE Straight PCB Solder
1x4 FEMALE Straight PCB Solder
1x6 FEMALE Straight PCB Solder
1x8 FEMALE Straight PCB Solder

Push On PCB Fastener & No Latch

Part	
Number	Description
PM103FBAOSP	1x3 FEMALE Straight PCB Solder
PM104FBAOSP	1x4 FEMALE Straight PCB Solder
PM106FBAOSP	1x6 FEMALE Straight PCB Solder
PM108FBAOSP	1x8 FEMALE Straight PCB Solder

Self-tapping Screws For PCB Mount & No Latch

Part		
Number	Description	
PM103FBAOST	1x3 FEMALE Straight PCB Solder	
PM104FBAOST	1x4 FEMALE Straight PCB Solder	
PM106FBAOST	1x6 FEMALE Straight PCB Solder	
PM108FBAOST	1x8 FEMALE Straight PCB Solder	

DS-PM1RF REV09