

## TC2W4

Wiring Duct Cover Width 2.00" PVC, White, 120' / Pkg. Qty.

Article Number: 181-92011

Part Number: TC2W4

Type: TC2

Material: PVC



### 1. Base Data

---

Part No.	TC2W4
----------	-------

Type	TC2
------	-----

Color	White
-------	-------

### 2. Product Dimensions

---

Length (L)	6 ft / 1.83 m
------------	---------------

Width (W)	2.00 " / 50.80 mm
-----------	-------------------

### 4. Material and Specifications

---

<b>Material</b>	Polyvinylchloride (PVC)
<b>Material Shortcut</b>	PVC
<b>Certification</b>	UL
<b>CSA Certified</b>	Yes
<b>Flammability</b>	self-extinguishing
<b>Operating Temperature</b>	+122 °F (+50 °C)

### **Logistic and Packaging**

---

<b>Packaging Type</b>	carton
<b>Pkg. Qty.</b>	120 ft / 36.6 m
<b>Carton Qty.</b>	120 ft
<b>UPC</b>	08930609557

### **Miscellaneous**

---

**UL Recognized (US and Canada)** Yes

## Covers

Covers for Pro-Duct wiring duct are sold separately. The covers are interchangeable among the 3 styles of duct (solid, slotted and high density).

For modular packaging, remove the last digit "4" from the HellermannTyton part number. e.g., TC1G = 1" wide cover/gray/modular packaging.



File # E64139 File # 49249

Product Selection						
Article No.	Part No.	Type	Width (W)		Color	Pkg. Qty.
			in.	(mm)		ft. (6 ft. lengths)
<b>.5" wide covers</b>						
181-00443	TC.5W4	TC.5	.76"	(19.30)	White	120 ft
181-00442	TC.5G4	TC.5	.76"	(19.30)	Gray	120 ft
181-90050	TC.5BK4	TC.5	.76"	(19.30)	Black	120 ft
<b>.75" wide covers</b>						
181-00447	TC.75W4	TC.75	1.01"	(25.65)	White	120 ft
181-00446	TC.75G4	TC.75	1.01"	(25.65)	Gray	120 ft
181-00445	TC.75BK4	TC.75	1.01"	(25.65)	Black	120 ft
<b>1" wide covers</b>						
181-91008	TC1W4	TC1	1.00"	(25.40)	White	120 ft
181-91004	TC1G4	TC1	1.00"	(25.40)	Gray	120 ft
181-91000	TC1BK4	TC1	1.00"	(25.40)	Black	120 ft
<b>1.5" wide covers</b>						
181-91510	TC1.5W4	TC1.5	1.50"	(38.10)	White	120 ft
181-91507	TC1.5G4	TC1.5	1.50"	(38.10)	Gray	120 ft
181-91503	TC1.5BK4	TC1.5	1.50"	(38.10)	Black	120 ft
<b>2" wide covers</b>						
181-92011	TC2W4	TC2	2.00"	(50.80)	White	120 ft
181-92005	TC2G4	TC2	2.00"	(50.80)	Gray	120 ft
181-92001	TC2BK4	TC2	2.00"	(50.80)	Black	120 ft
<b>3" wide covers</b>						
181-93011	TC3W4	TC3	3.00"	(76.20)	White	120 ft
181-93008	TC3G4	TC3	3.00"	(76.20)	Gray	120 ft
181-93003	TC3BK4	TC3	3.00"	(76.20)	Black	120 ft
<b>4" wide covers</b>						
181-94014	TC4W4	TC4	4.00"	(101.60)	White	120 ft
181-94009	TC4G4	TC4	4.00"	(101.60)	Gray	120 ft
181-94003	TC4BK4	TC4	4.00"	(101.60)	Black	120 ft
<b>6" wide covers</b>						
181-96002	TC6W4	TC6	6.00"	(152.40)	White	60 ft
181-96000	TC6G4	TC6	6.00"	(152.40)	Gray	60 ft
181-00448	TC6BK4	TC6	6.00"	(152.40)	Black	60 ft
<b>8" wide covers</b>						
181-00451	TC8W4	TC8	8.00"	(203.20)	White	60 ft
181-00450	TC8G4	TC8	8.00"	(203.20)	Gray	60 ft
181-00449	TC8BK4	TC8	8.00"	(203.20)	Black	60 ft

Dimensions are approximate and subject to technical changes. Use **Part No.** for ordering and **Type** for specification purposes.