HellermannTyton

132-00010



Article Number: 132-00010

Button Head Tie, 105lb, 9.6" Long, Max Bundle Diameter 2.6", PA66HSUV, Black, 50/pkg





Base Data

Local Order Number 132-00010

Type BT105R

Color Black (BK)

Features and Benefits • Unique two piece tie allows parallel entry and exit through the head for easy assembly.

• PA66HIRHS material make it ideal for trucking and heavy equipment applications.

Product Description The button head tie is a two piece tie providing for parallel entry and exit through the head. The strap contains

serrations on both sides, and has two opposed pawls recessed within a domed head. This design allows the strap to

be directed clockwise or counter-clockwise prior to insertion into the head, enabling bi-directional looping.

Short Description Button Head Tie, 105lb, 9.6" Long, Max Bundle Diameter 2.6", PA66HSUV, Black, 50/pkg

Product Dimensions

Minimum Tensile Strength (Imperial) 105.0 lbs

Minimum Tensile Strength (Metric) 467 N

Length L (Imperial) 9.6 "

Length L (Metric) 244.4 mm

Fixation Method Connector Clip

Tie Closure plastic pawl

Variant Outside Serrated

Width W (Imperial) 0.2 "

Width W (Metric) 5.6 mm

Bundle Diameter Min. (Imperial) 0.06 "

Bundle Diameter Min. (Metric) 1.5 mm

Bundle Diameter Max. (Imperial) 2.6 "

Bundle Diameter Max. (Metric) 66.7 mm

Logistics and Packaging

Quantity Per bag

Package Quantity (Metric) 50

Carton Quantity 1000

Material and Specifications

Material Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)

Material Shortcut PA66HIRHSUV

Material Cable Tie Polyamide 6.6 high impact modified, heat stabilized, UV resistant (PA66HIRHS)

Flammability UL94 HB

Material Head Polyamide 6.6 heat stabilized (PA66HS)

 $\textbf{Operating Temperature} \quad \text{-65}^{\circ}\text{F to +212}^{\circ}\text{F (-54}^{\circ}\text{C to +100}^{\circ}\text{C)}$

© HellermannTyton 2015