

151-03403

Article Number: 151-03403

Edge Clip and Tape Clip, EC17, Panel Thickness 0.04" - 0.12", 1.8" Long, PA66HIRHS, Black, 500/pkg



Download drawing



Download spec sheet

Base Data

Local Order Number 151-03403

Type EC17

Color Black (BK)

Features and Benefits

- Edge Clip applies easily to plastic and metal sheets without the need for a mounting hole.
- Edge Clip provides low insertion force and high extraction force ideal for assembly environments.

Product Description HellermannTyton's edge clip and tape clip assembly is ideal for use in applications where holes are not acceptable. Edge clips are widely used for fixing and bundling cables and wires within the automobile, harness making, panel building and electrical industries

Short Description Edge Clip and Tape Clip, EC17, Panel Thickness 0.04" - 0.12", 1.8" Long, PA66HIRHS, Black, 500/pkg

Product Dimensions

Length L (Imperial) 1.8 "

Length L (Metric) 46.5 mm

Fixation Method Edge Clips

Width W (Imperial) 0.39 "

Width W (Metric) 10.0 mm

Height H (Imperial) 0.51 "

Height H (Metric) 13.0 mm

Panel Thickness Max. (Imperial) 0.12 "

Panel Thickness Max. (Metric) 3.0 mm

Panel Thickness Min. (Imperial) 0.04 "

Panel Thickness Min. (Metric) 1.0 mm

Logistics and Packaging

Quantity Per bag

Package Quantity (Metric) 500 Pieces

Carton Quantity 7000 Pieces

Weight (Metric) 1.25 kg

Material and Specifications

Material Polyamide 6.6 high impact modified, heat stabilized, UV resistant (PA66HIRHS)

Material Shortcut PA66HIRHS

Flammability UL94 HB

Operating Temperature -40°F to +221°F (-40°C to +105°C)

ROHS Compliant Yes

© HellemannTyton 2015