# HellermannTyton

#### DCT90HIRK2



Article Number: 115-30900

Dual Clamp Tie 150 lb, Length 13", Max Bun Dia 1.3", Width .5", PA66HIRHS, Black 50/pkg

RoH!



#### **Base Data**

Local Order Number DCT90HIRK2

Type DCT9

Color Black (BK)

Features and Benefits • Provides dual separation between bundles to prevent chaffing and abrasion.

• 150 lb. tensile strength ensures enough strength for heavy duty applications.

· Straps are releasable for increased serviceability.

Product Description HellermannTyton's dual clamp ties are designed to provide parallel separation between hoses, wires, cables and

tubing, protecting them from abrasion. These ties have an optional mounting hole for securing bundles along the chassis of tracks, trailers, and heavy duty equipment. The unique one-piece design features the dual head centered

on the strap.

Short Description Dual Clamp Tie 150 lb, Length 13", Max Bun Dia 1.3", Width .5", PA66HIRHS, Black 50/pkg

## **Product Dimensions**

Minimum Tensile Strength (Imperial) 150.0 lbs

Length L (Imperial) 13.0 "

Length L (Metric) 331.0 mm

Fixation Method Weld Stud Fixing

Identification Plate Position none

Releasable Closure No

Tie Closure plastic pawl

Variant Inside Serrated

Width W (Imperial) 0.5 "

Width W (Metric) 12.7 mm

Height H (Imperial) 0.8 "

Height H (Metric) 19.3 mm

Bundle Diameter Max. (Imperial) 1.3 "

Bundle Diameter Max. (Metric) 33.0 mm

Stud Size (Imperial) 0.25 "

Stud Size (Metric) 6.35 mm

### **Logistics and Packaging**

Quantity Per bag

Package Quantity (Metric) 50

Carton Quantity 400 Pieces

Weight (imperial) 0.5 lbs
Weight (Metric) 12 kg

## **Material and Specifications**

Material Polyamide 6.6 high impact modified, heat stabilized, UV resistant (PA66HIRHS)

Material Shortcut PA66HIRHS

Flammability UL94 HB

**Operating Temperature** -40°F to +230°F (-40°C to +110°C)

ROHS Compliant Yes