# **HellermannTyton**


## 132-00009



Article Number: 132-00009

Button Head Tie with Retainers and Pilot Bushings, 15.0" Long, PA66HIRHSUV, Black, 50/pkg





#### **Base Data**

Local Order Number 132-00009

Type BT130LDP

Color Black (BK)

Features and Benefits • Unique two piece tie allows parallel entry and exit through the head for easy assembly.

· High impact, heat stabilized material gives strength needed for trucking and heavy equipment applications.

Product Description The button head tie is a two piece tie providing for parallel entry and exit through the head. The strap contains

serrations on both sides, and has two opposed pawls recessed within a domed head. This design allows the strap to

be directed clockwise or counter-clockwise prior to insertion into the head, enabling bi-directional looping.

Short Description Button Head Tie with Retainers and Pilot Bushings, 15.0" Long, PA66HIRHSUV, Black, 50/pkg

#### **Product Dimensions**

Minimum Tensile Strength (Imperial) 130.0 lbs

Minimum Tensile Strength (Metric) 578 N

Length L (Imperial) 15.0 "

Length L (Metric) 381.5 mm

Fixation Method Connector Clip

Tie Closure plastic pawl

Variant Outside Serrated

Width W (Imperial) 0.3 "

Width W (Metric) 7.6 mm

Bundle Diameter Min. (Imperial) 0.06 "

Bundle Diameter Min. (Metric) 1.5 mm

Bundle Diameter Max. (Imperial) 4.3 "

Bundle Diameter Max. (Metric) 110.0 mm

#### **Logistics and Packaging**

Quantity Per bag

Package Quantity (Metric) 50

Carton Quantity 1000

### **Material and Specifications**

Material Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)

Material Shortcut PA66HIRHSUV

Flammability UL94 HB

Material Head Polyamide 6.6 heat stabilized (PA66HS)

**Operating Temperature** -40°F to +185°F (-40°C to +85°C)

© HellermannTyton 2015