

156-00538



Article Number: 156-00538

Cable Tie and Edge Clip, 50lb, 8.0" Long, EC4B, Panel Thickness .04"-.12", PA66HS, Black, 500/bag



Download drawing



Download spec sheet

Base Data

Local Order Number 156-00538
Type T50REC4B
Color Black (BK)

Features and Benefits

- Edge Clip applies easily to plastic and metal sheets without the need for a mounting hole.
- Edge Clip provides low insertion force and high extraction force ideal for assembly environments.
- Two piece assembly allows the mount to slide along the strap ensuring proper orientation.
- Cable tie is outside serrated to reduce bundle chafing.

Product Description The cable tie and edge clip assembly is ideal for use where holes are not acceptable or where adhesives will fail due to temperature problems. Edge clips are widely used for fixing and bundling cables and wires within automotive, trucking, heavy equipment, solar panel, wind power, and white goods equipment manufacturing.

Short Description Cable Tie and Edge Clip, 50lb, 8.0" Long, EC4B, Panel Thickness .04"-.12", PA66HS, Black, 500/bag

Product Dimensions

Minimum Tensile Strength (Imperial) 50.0 lbs
Minimum Tensile Strength (Metric) 225 N
Length L (Imperial) 8.0 "
Length L (Metric) 200 mm
Length L2 (Imperial) 0.55 "
Length L2 (Metric) 14.0 mm
Fixation Method EdgeClip, top, assembled, 2 piece
Identification Plate Position none
Releasable Closure No
Variant Inside Serrated
Width W (Imperial) 0.18 "
Width W (Metric) 4.6 mm
Width W2 (Imperial) 0.45 "
Width W2 (Metric) 11.5 mm
Height H (Imperial) 0.05 "
Height H (Metric) 1.2 mm
Height H2 (Imperial) 0.4 "
Height H2 (Metric) 10.8 mm
Bundle Diameter Min. (Imperial) 0.06 "
Bundle Diameter Min. (Metric) 4.0 mm
Bundle Diameter Max. (Imperial) 2.0 "

Bundle Diameter Max. (Metric)	45.0 mm
Panel Thickness Max. (Imperial)	0.12 "
Panel Thickness Max. (Metric)	3.0 mm
Panel Thickness Min. (Imperial)	0.04 "
Panel Thickness Min. (Metric)	1.0 mm
Thickness T (Imperial)	0.05 "
Thickness T (Metric)	1.2 mm

Logistics and Packaging

Quantity Per	bag
Package Quantity (Metric)	500
Carton Quantity	4000
Weight (Metric)	4.5 kg

Material and Specifications

Material	Polyamide 6.6 high impact modified, heat stabilized, UV resistant (PA66HIRHS) Polyamide 6.6 heat stabilized (PA66HS)
Material Shortcut	PA66HS PA66HIRHS
Material Cable Tie	Polyamide 6.6 heat stabilized (PA66HS)
Flammability	UL94 HB
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
ROHS Compliant	Yes