

805-0974

156-00306

Omega Clip Tie, 50lbs, Clip Dia .16"-.4" Max Bun Dia. 1.38" PA66HS Tie, HIRHS MNT, BLK 500/pk

Article Number: 156-00306

Part Number: 156-00306

Type: T50ROC1B



Base Data

Part No. 156-00306

Type T50ROC1B

Color Black

Features Omega Clips secure cables to tubular frame rails. The cable tie is fastened to the tubular frame rail and the solar cable snaps into the clip. The cable can be removed from the clip and reinstalled without additional fasteners.

Anti rotation (Yes / No) NO

Identification Plate Position none

Tie Closure plastic pawl

Product Dimensions

Min. Tensile Strength 50 lbs / 225 N

Length (L) 7.9 " / 200 mm

Attach to Diameter 0.16 " - 0.40 "

Width (W) .181 " / 4.6 mm

Height (H) 0.05 " / 1.2 mm

Min. Ø Bundle .16 " / 4.0 mm

Max. Ø Bundle 1.8 " / 45.0 mm

Attach to Ø 4.0 - 10.0

Thickness 1.2

Material and Specifications

Material Polyamide 6.6 heat stabilized (PA66HS) / Polyamide 6.6 high impact modified, heat stabilized, UV resistant (PA66HIRHS)

Cable Tie Polyamide 6.6 heat stabilized (PA66HS)