# HellermannTyton

## MK7-449



Download spec sheet

#### E

PDF

Base Data	
Local Order Number	MK7-449
Туре	MK7-449
Features and Benefits	<ul> <li>An easy to read display speeds adjustment and verification.</li> <li>On the Mark 7, a larger knob sets the three variable tension levels (minimum, intermediate, and standard). The smaller knob fine tunes within the tension range.</li> <li>The larger knob on the Mark 9 sets to two variable tension levels (standard and heavy). The smaller knob fine tunes the tension setting.</li> <li>Housings are manufactured from a high impact, glass reinforced nylon.</li> <li>A double wall linkage adds more strength.</li> <li>Tough chromium steel components ensure longevity.</li> <li>MK7 &amp; MK9 are military specified.</li> <li>Single and dual lock-out features available for tensioning ranges.</li> <li>Cable tie tension and cut-off tools reduce operator fatigue and speed assembly.</li> <li>The Mark 7 features a one inch stroke, while the Mark 9 has a 5/8 inch stroke.</li> <li>Both reduce trigger cycles required to install cable ties.</li> <li>Ergonomic design on both tools ideally fit the operator's hand. Removable padded hand grips further reduce impact to the hand.</li> <li>Low friction bearing mechanisms reduce hand effort and provide a smooth stroke.</li> <li>Extremely light, the Mark 7 weighs only 10 ounces. The Mark 9 weighs just 13 ounces.</li> <li>Quick tension adjustability for flush cut-off.</li> </ul>
Short Description	Replacement blade for Mark 7 series tools.

#### **Product Dimensions**

Tension Setting Tools Adjustable

#### Logistics and Packaging

Quantity Per bag

Package Quantity 1

### **Material and Specifications**

ROHS Compliant Yes

© HellermannTyton 2015