

T120MR0K2

Article Number: 113-12020

Screw Mount Tie, 18lb, 4.3" Long, Max Bun Diameter 4.02", #1/4 Screw, PA66, Black, 50/pkg



Download drawing



Download spec sheet

Base Data

Local Order Number T120MR0K2

Type T120MR

Color Black (BK)

Features and Benefits

- Part design applies easily to any #1/4" Screw
- Stud style provides low insertion and high extraction force.

Product Description Screw Mount Cable Ties are made of all plastic and provide a quick and simple method of mounting.

Short Description Screw Mount Tie, 18lb, 4.3" Long, Max Bun Diameter 4.02", #1/4 Screw, PA66, Black, 50/pkg

Product Dimensions

Minimum Tensile Strength (Imperial) 120.0 lbs

Minimum Tensile Strength (Metric) 535 N

Length L (Imperial) 15.6 "

Length L (Metric) 395.0 mm

Fixation Method fixing hole

Identification Plate Position none

Releasable Closure No

Tie Closure plastic pawl

Variant Inside Serrated

Width W (Imperial) 0.3 "

Width W (Metric) 7.6 mm

Height H (Imperial) 0.31 "

Height H (Metric) 7.9 mm

Bundle Diameter Min. (Imperial) 0.2 "

Bundle Diameter Min. (Metric) 5.0 mm

Bundle Diameter Max. (Imperial) 4.0 "

Bundle Diameter Max. (Metric) 102.0 mm

Mounting Hole Diameter D (Imperial) 0.26 "

Mounting Hole Diameter D (Metric) 6.5 mm

Thickness T (Imperial) 0.07 "

Mounting Hole Diameter D Max. 6.5 mm

(Metric) Mounting Hole Diameter D Min. (Metric) 6.5 mm

Thickness T (Metric) 1.8 mm

Logistics and Packaging

Quantity Per	bag
Package Quantity (Metric)	50 Pieces
Carton Quantity	1000 Pieces
Weight (Metric)	5.8 kg

Material and Specifications

Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Flammability	UL94 V2
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
ROHS Compliant	Yes
UL Listed (US and Canada)	No
UL Recognized (US and Canada)	Yes