

### Quality Enclosures. Service Excellence.

## Small Hinged Cover Enclosures - Type 3R with Knockouts



#### Application

- Designed for use as a wiring/junction box.
- Provides protection against rain, sleet, snow and dripping water.

#### Standards

- UL-50 Type 3R
- CSA Type 3R Complies with
  NEMA Type 3R
  - IEC 60529, IP32

#### Construction

- Formed and spot welded from 16 gauge galvanized steel.
- Drip-shield top and seam-free sides, front and back.
- Galvanized steel hinge has stainless steel pin.
- Provisions for padlocking on zinc-plated draw pull catch.
- Easily removed knockouts on bottom of enclosure.
- Panel studs provided for mounting optional panels.
- External mounting feet
- Oil resistant gaskets are permanently secured.





#### Finish

• Enclosure and cover are finished in ANSI/ASA 61 gray powder coating.


#### Accessories

Inner Panel



Quality Enclosures. Service Excellence.

# Small Hinged Cover Enclosures - Type 3R with Knockouts



	<b>Optional Panel</b>		в	с	Panel Size		Mounting	<b>Overall Dimensions</b>		Knockout	Shipping
Part Number	Part Number	Α			D	Е	F	G	н	Pattern	Wt. Ibs
C3R644HCR	N1JP64	6	4	4	4.25	2.25	7.00	8.00	5.10	2-3-4	3
C3R664HCR	N1JP66	6	6	4	4.25	4.25	7.00	8.00	7.10	2-3-4	5
C3R864HCR	N1JP86	8	6	4	6.25	4.25	9.00	10.00	7.10	2-3-4	6
C3R886HCR	N1JP88	8	8	6	6.25	6.25	9.00	10.00	9.10	6-7-8-9	8
C3R1086HCR	N1JP108	10	8	6	8.25	6.25	11.00	12.00	9.10	6-7-8-9	9
C3R12106HCR	N1JP1210	12	10	6	10.25	8.25	13.00	14.00	11.10	3-4-5-6-7	11
C3R12126HCR	N1JP1212	12	12	6	10.25	10.25	13.00	14.00	13.10	3-4-5-6-7	13
C3R121210HCR	N1JP1212	12	12	10	10.25	10.25	13.00	14.00	13.10	3-4-5-6-7	20