

Wall Mount - Side Hinged - Bracket Racks (HPB & APB Series)

Path: Home > Rack Index > Wallmount - Side Hinged Bracket Racks (HPB & APB Series)




Features:

- Adjustable depth bracket rack for 19" rack mount equipment...
- Full EIA hole centers (5/8 5/8 1/2 inch spacing) drilled and tapped for 10-32 hardware...
- Double hinged on one side to access rear of equipment...
- Smooth 8" x 2.5" hole on the rear for wire access...
- Includes mounting template for easy installation...
- Adjustable depth from 12 to 18"...
- Rear mounting holes are key holes for easy installation...
- Multiple cable lacing tie offs punched into unit...
- Includes 10-32 black rack screws with integral factory installed, mar resistant black nylon washer...
- 16 gauge formed steel...
- Weight load tested (APB19007) to 70 pounds...
- Rugged textured black powder paint finish...
- Wall mounting hardware not included...

Part Number	Drawing File Size	AutoCAD .dxf File (zipped)	.zip File Size	Panel Height	
				Inches	Units
APB19007BK1	61K		45K	7.00	4
APB19010BK1	64K		50K	10.50	6
APB19014BK1	68K		56K	14.00	8

PART No. APB19007BK1



Wall Moun

Bracket - Side Hinged (HPB & APB Series)

FIXED DEPTH

FEATURES

- · Economical bracket rack for 19" rack mount
- Full EIA hole centers (5/8 5/8 1/2 inch spacing)
- · Hinged on one side
- Quantity 3 1 1/8" diameter knockouts on the rear
- 6" deep
- · Rear has key holes for ease of wall mounting
- Includes quantity 8, 10-32 clip nuts and screws
- 16 gauge formed steel
- Weight load tested (HPB19005) to 100 pounds
- Rugged textured black powder paint finish.



Part Number	Panel Height		
rait Number	Inches	Units	
HPB19003BK1	3.50	2	
HPB19005BK1	5.25	3	
HPB19007BK1	7.00	4	

ADJUSTABLE DEPTH

FEATURES

- Adjustable depth bracket rack for 19" rack mount
- Full EIA hole centers (5/8 5/8 1/2 inch spacing)
- Double hinged (one on each side) to allow access to deep equipment
- Quantity 3 1 1/8" knockouts on the rear
- Adjustable depth from 12 to 18"
- Rear has key holes for ease of wall mounting
- Multiple slots for cable ties (4 rubber wall spacers included)
- Includes quantity 8, 10-32 clip nuts and screws
- 16 gauge formed steel
- Weight load tested (APB19007) to 70 pounds
- · Rugged textured black powder paint finish.

Part Number	Panel Height		
Part Number	Inches	Units	
APB19007BK1	7.00	4	
APB19014BK1	14.00	8	



