

Table Top Rack Cabinets (RCHS Series) - *HEAVY DUTY*



Textured - Light Gray (RAL7035)

Features:

- Heavy duty, 16-gauge steel, 19" table top rack cabinet...
- For ventilated versions link to our <u>RCHV</u> <u>series</u>...
- Panel rails are infinitely adjustable (front to back), round hole punched for 10-32 clip-nuts to full EIA hole centers (5/8 5/8 1/2 inch spacing)...
- Includes two pairs of rails (for rear support of heavier equipment), rubber feet, black ABS plastic handles, a starter pack of 10-32 clip nuts & matching **1421ABK** black screws...
- Supplied unassembled (four cabinet pieces & four rails), shipped in a flat pack container for handling ease & protection (see photo below)...
- Simple assembly using one bolt in each corner to lock the sides to the top and bottom (hardware included)...
- Overall width 21"...
- Overall height 2" over panel space...
- Front & back lip is .585" so usable depth is reduced by 1.17"
- Recommended maximum weight (RCHS1902824 tested) 800 pounds...
- Rugged textured powder paint finish...
- Stocked in Black & Light Gray (RAL7035)...

17.5" Deep models:

[gas]

| Part Number Color | | der. | AutoCAD .dxf File | Panel Height | | Number of Clip Nuts | |
|--|-------|----------------|----------------------|--------------|-------|------------------------|----|
| | | Reader File | | Inches | Units | | |
| RCHS1900817BK1 RCHS1900817CG1 RCHS1900817LG1 | Beige | 63K | ZIP 59K | 8.75 | 5 | 8 | 38 |
| RCHS1901017BK1 RCHS1901017CG1 RCHS1901017LG1 | Beige | 60K | ZIP 61K | 10.50 | 6 | 16 | 40 |
| RCHS1901417BK1 RCHS1901417CG1 RCHS1901417LG1 | Beige | 64K | ZIP 60K | 14.00 | 8 | 16 | 44 |
| RCHS1901717BK1 RCHS1901717CG1 RCHS1901717LG1 | Beige | 67K | ZIP 63K | 17.50 | 10 | 16 | 50 |
| RCHS1902217BK1 RCHS1902217CG1 RCHS1902217LG1 | Beige | 70K | ZIP 65K | 22.75 | 13 | 16 | 54 |
| RCHS1902817BK1 RCHS1902817CG1 RCHS1902817LG1 | Beige | 72K | ZIP 67K | 28.00 | 16 | 16 | 60 |

24.5" Deep models:


| Part Number | Color | Reader File | .dxf File | Panel I | | Number of Clip Nuts Included | |
|--|-------|----------------|------------|---------|----|------------------------------------|----|
| RCHS1901024BK1 RCHS1901024CG1 RCHS1901024LG1 | Beige | 20E | ZIP 60K | 10.50 | 6 | 16 | 52 |
| RCHS1901424BK1 RCHS1901424CG1 RCHS1901424LG1 | Beige | 64K | ZIP 60K | 14.00 | 8 | 16 | 58 |
| RCHS1901724BK1 RCHS1901724CG1 RCHS1901724LG1 | Beige | 64K | ZIP 60K | 17.50 | 10 | 16 | 62 |
| RCHS1902224BK1 RCHS1902224CG1 RCHS1902224LG1 | Beige | 66K | ZIP 60K | 22.75 | 13 | 16 | 70 |

| RCHS1902824BK1 | Black | POF | | | | | |
|----------------|------------|-----|-----|-------|----|----|----|
| RCHS1902824CG1 | Beige | D | ZIP | 28.00 | 16 | 16 | 78 |
| RCHS1902824LG1 | Light Gray | 82K | 60K | | | | |

31.5" Deep models:

| Part Number | Color | Reader File | .dxf File | Panel Height | | Number of Clip Nuts | |
|----------------------------------|-------|----------------|------------|--------------|-------|------------------------|----|
| | | | | Inches | Units | Included | |
| RCHS1901031BK1 RCHS1901031LG1 | | 62K | ZIP 54K | 10.50 | 6 | 16 | 64 |
| RCHS1901431BK1 RCHS1901431LG1 | | 63K | ZIP 54K | 14.00 | 8 | 16 | 68 |
| RCHS1901731BK1 RCHS1901731LG1 | | 63K | ZIP 53K | 17.50 | 10 | 16 | 74 |
| RCHS1902231BK1 RCHS1902231LG1 | | 65K | ZIP 53K | 22.75 | 13 | 16 | 86 |
| RCHS1902831BK1 RCHS1902831LG1 | | 66K | ZIP 54K | 28.00 | 16 | 16 | 94 |

Feature Views:





Accessories:



Casters - Part Number 1425PHD

- SOLD IN A SET OF 4
- Base of cabinet is punched to accept this caster set
- 600# Mfg's specified weight capacity (Set of 4)
- Features ball bearing swivel and hard composition wheels
- Small foot print 2.125" x 15/16" hole mounting pattern
- Wheels are grey & 2" wheel diameter (adds only 2.5" to overall rack height).
- Includes mounting hardware



Doors

- 16-gauge steel construction
- Both front & back of "RCHS" rack cabinets are punched to accept these doors
- Mounts either right or left hand hinge (door & cabinet are symmetrical)
- Includes installed lock and two keys
- Finished in rugged textured powder paint to match RCHS/RCHV enclosures
- Includes mounting hardware



| | | File | (zipped) | Panel Height | IDS. |
|---|---------------------------------|------|------------|------------------|------|
| RCHD1908BK1 RCHD1908CG1 RCHD1908LG1 | Black Beige Light Gray | 17K | ZIP 17K | 8" (5 U) | 5 |
| RCHD1910BK1 RCHD1910CG1 RCHD1910LG1 | Black Beige Light Gray | 18K | ZIP 18K | 10.5" (6 U) | 5 |
| RCHD1914BK1 | Black Beige Light Gray | 19K | ZIP 20K | 14" (8 U) | 6 |
| RCHD1917BK1 RCHD1917CG1 RCHD1917LG1 | Black Beige Light Gray | 21K | ZIP 22K | 17.5" (10 U) | 7 |
| RCHD1922BK1 RCHD1922CG1 RCHD1922LG1 | Black Beige Light Gray | 22K | ZIP 24K | 22.75" (13 U) | 9 |
| RCHD1928BK1 RCHD1928CG1 RCHD1928LG1 | Black Beige Light Gray | 24K | ZIP 27K | 28" (16 U) | 12 |



Extra Panel Rails

- RCHS rack cabinets ship with two pair order below for extra mounting capabilities
- Sold in pairs
- Finished in rugged black textured powder paint
- Includes amhal strut mounting hardware (black clip nuts are not included)

| Part Number | Use With Cabinet Panel Height |
|-----------------|----------------------------------|
| RCHR1908 | 8" (5 U) |
| RCHR1910 | 10.5" (6 U) |
| RCHR1914 | 14" (8 U) |
| RCHR1917 | 17.5" (10 U) |
| RCHR1922 | 22.75" (13 U) |

RCHR1928 28" (16 U)



Extra Spring Nuts - Part Number 1421SN

- 1/4 20 Strut nut
- 1/4 20 x 1/2 bolt
- Used only in our RCHS & RCHV table top rack cabinets handy for mounting of other equipment to the horizontal struts
- Sold in packages of 8 (8 spring nuts and 8 bolts) as shown



Replacement Rubber Feet - Part Number 1421RC24

- RCHS rack cabinets ship with four feet included order these for replacement
- Sold in package of 20

