Advanced Part Search

Literature Corporate * **Contact Us**

English | Français

News Home

Pre-Assembled C2 Cabinet C2RR Series

Products *

Home / Racks & Cabinets / Cabinets /







Features

- Heavy duty welded rack 1,500 lb (682 kg.) even load rating.
- Heavy duty: 14 gauge welded steel frame, 16 gauge side panels.
- · Rails are made of 10 gauge zinc plated steel.
- Recommended maximum weight (C2F247836 tested) 1,500 pounds (682

Resources *

Finished in a rugged, textured powder paint finish.

Distributors

- RoHS Compliant.
- · Manufactured in North America.
- Note: "CG1" (Beige color) is being phased out from stock replaced with "LG1" a light gray (RAL7035).
- If you would rather build your own system see our "Contempra 2" system.

• All configurations include:

- o One (1) Welded C2 Cabinet Frame
- o Two (2) Removable Side Panels (with 1/4 turn latches)
- o Four (4) Leveling Feet
- o Eight (8) Keys
- Starter pack of 10-32 Screws (and cage nuts when applicable).

• C2RR Series Specific Components Include:

- o Four (4) Infinitely Adjustable Tapped 10-32 Combination Mounting Rails
- One (1) Solid Locking Door
- One (1) Solid Top Panel

• C2RR "D" Series Specific Components include:

- o Four (4) Infinitely Adjustable Tapped 10-32 Combination Mounting Rails
- One (1) Window Front Locking Door (Note: CG1 assembly includes a BK1 door)
- o One (1) Louvered Rear Locking Door
- One (1) Vented Top Panel with Four (4) 3.5" (89 mm) diameter cable access holes with covers

Gallery







Accessories



Cabinet Fan Tops



Vertical Cabinet Cable Manager




Two Post Mounting Cantilever Shelf













C2/C3 Bolt Down Kit

C2RR Rapid Rack

Click part number for details (e.g., CAD files, assembly instructions)

Units shown: inch. Switch units to: mm

Part No.	Part No.	Part No.	Overall Dimensions			Usable Mounting Dimensions			Shipping
Black	Beige*	Light Gray	Height	Width	Depth	Height	Width	Rack Units	Weight
C2RR194223BK1	C2RR194223CG1	C2RR194223LG1	49.31	23.00	23.63	42.06	19.00	24U	170
C2RR196323BK1	C2RR196323CG1	C2RR196323LG1	70.31	23.00	23.63	63.06	19.00	36U	218
C2RR197023BK1	C2RR197023CG1	C2RR197023LG1	77.31	23.00	23.63	70.06	19.00	40U	230
C2RR197823BK1	C2RR197823CG1	C2RR197823LG1	86.06	23.00	23.63	78.81	19.00	45U	254
C2RR194231BK1	C2RR194231CG1	C2RR194231LG1	49.31	23.00	31.50	42.06	19.00	24U	194
C2RR196331BK1	C2RR196331CG1	C2RR196331LG1	70.31	23.00	31.50	63.06	19.00	36U	250
C2RR197031BK1	C2RR197031CG1	C2RR197031LG1	77.31	23.00	31.50	70.06	19.00	40U	268
C2RR197831BK1	C2RR197831CG1	C2RR197831LG1	86.06	23.00	31.50	78.81	19.00	45U	290

C2RR "D" Series LAN/Data Rapid Rack

Click part number for details (e.g., CAD files, assembly instructions)

Units shown: inch. Switch units to: mm

Office shown. Inch. Switch units to. IIII										
Part No.	Part No.	Part No.	Overall Dimensions			Usable Mounting Dimensions			Shipping	
Black	Beige*	Light Gray	Height	Width	Depth	Height	Width	Rack Units	Weight	
C2RR197023DBK1	C2RR197023DCG1	C2RR197023DLG1	77.31	23.00	23.63	70.06	19.00	40U	295	
C2RR197823DBK1	C2RR197823DCG1	C2RR197823DLG1	86.06	23.00	23.63	78.81	19.00	45U	330	
C2RR197031DBK1	C2RR197031DCG1	C2RR197031DLG1	77.31	23.00	31.50	70.06	19.00	40U	315	
C2RR197831DBK1	C2RR197831DCG1	C2RR197831DLG1	86.06	23.00	31.50	78.81	19.00	45U	355	
C2RR247023DBK1	C2RR247023DCG1	-	77.31	28.00	23.63	70.06	24.00	40U	325	
C2RR247823DBK1	C2RR247823DCG1	-	86.06	28.00	23.63	78.81	24.00	45U	342	
C2RR247031DBK1	C2RR247031DCG1	-	77.31	28.00	31.50	70.06	24.00	40U	346	
C2RR247831DBK1	C2RR247831DCG1	-	86.06	28.00	31.50	78.81	24.00	45U	363	

Need Assistance? Contact Us.

Data subject to change without notice.

Home Back to Top Contact Us Login | f | l in

© 2013. Hammond Manufacturing Ltd. All rights reserved.



