

Table Top Rack Cabinets (RCHS Series) - *HEAVY DUTY*



Textured - Light Gray (RAL7035)

Features:

- Heavy duty, 16-gauge steel, 19" table top rack cabinet...
- For ventilated versions link to our <u>RCHV</u> <u>series</u>...
- Panel rails are infinitely adjustable (front to back), round hole punched for 10-32 clip-nuts to full EIA hole centers (5/8 5/8 1/2 inch spacing)...
- Includes two pairs of rails (for rear support of heavier equipment), rubber feet, black ABS plastic handles, a starter pack of 10-32 clip nuts & matching **1421ABK** black screws...
- Supplied unassembled (four cabinet pieces & four rails), shipped in a flat pack container for handling ease & protection (see photo below)...
- Simple assembly using one bolt in each corner to lock the sides to the top and bottom (hardware included)...
- Overall width 21"...
- Overall height 2" over panel space...
- Front & back lip is .585" so usable depth is reduced by 1.17"
- Recommended maximum weight (RCHS1902824 tested) 800 pounds...
- Rugged textured powder paint finish...
- Stocked in Black & Light Gray (RAL7035)...

17.5" Deep models:

[gas]

Part Number Color		der.	AutoCAD .dxf File	Panel Height		Number of Clip Nuts	
Turv (umber		Reader File		Inches	Units		
RCHS1900817BK1 RCHS1900817CG1 RCHS1900817LG1	Beige	63K	ZIP 59K	8.75	5	8	38
RCHS1901017BK1 RCHS1901017CG1 RCHS1901017LG1	Beige	60K	ZIP 61K	10.50	6	16	40
RCHS1901417BK1 RCHS1901417CG1 RCHS1901417LG1	Beige	64K	ZIP 60K	14.00	8	16	44
RCHS1901717BK1 RCHS1901717CG1 RCHS1901717LG1	Beige	67K	ZIP 63K	17.50	10	16	50
RCHS1902217BK1 RCHS1902217CG1 RCHS1902217LG1	Beige	70K	ZIP 65K	22.75	13	16	54
RCHS1902817BK1 RCHS1902817CG1 RCHS1902817LG1	Beige	72K	ZIP 67K	28.00	16	16	60

24.5" Deep models:


Part Number	Color	Reader File	.dxf File	Panel I		Number of Clip Nuts Included	
RCHS1901024BK1 RCHS1901024CG1 RCHS1901024LG1	Beige	20E	ZIP 60K	10.50	6	16	52
RCHS1901424BK1 RCHS1901424CG1 RCHS1901424LG1	Beige	64K	ZIP 60K	14.00	8	16	58
RCHS1901724BK1 RCHS1901724CG1 RCHS1901724LG1	Beige	64K	ZIP 60K	17.50	10	16	62
RCHS1902224BK1 RCHS1902224CG1 RCHS1902224LG1	Beige	66K	ZIP 60K	22.75	13	16	70

RCHS1902824BK1	Black	POF					
RCHS1902824CG1	Beige	D	ZIP	28.00	16	16	78
RCHS1902824LG1	Light Gray	82K	60K				

31.5" Deep models:

Part Number	Color	Reader File	.dxf File	Panel Height		Number of Clip Nuts	
				Inches	Units	Included	
RCHS1901031BK1 RCHS1901031LG1		62K	ZIP 54K	10.50	6	16	64
RCHS1901431BK1 RCHS1901431LG1		63K	ZIP 54K	14.00	8	16	68
RCHS1901731BK1 RCHS1901731LG1		63K	53K	17.50	10	16	74
RCHS1902231BK1 RCHS1902231LG1		65K	ZIP 53K	22.75	13	16	86
RCHS1902831BK1 RCHS1902831LG1		66K	ZIP 54K	28.00	16	16	94

Feature Views:





Accessories:



Casters - Part Number 1425PHD

- SOLD IN A SET OF 4
- Base of cabinet is punched to accept this caster set
- 600# Mfg's specified weight capacity (Set of 4)
- Features ball bearing swivel and hard composition wheels
- Small foot print 2.125" x 15/16" hole mounting pattern
- Wheels are grey & 2" wheel diameter (adds only 2.5" to overall rack height).
- Includes mounting hardware



Doors

- 16-gauge steel construction
- Both front & back of "RCHS" rack cabinets are punched to accept these doors
- Mounts either right or left hand hinge (door & cabinet are symmetrical)
- Includes installed lock and two keys
- Finished in rugged textured powder paint to match RCHS/RCHV enclosures
- Includes mounting hardware



		File	(zipped)	Panel Height	IDS.
RCHD1908BK1 RCHD1908CG1 RCHD1908LG1	Black Beige Light Gray	17K	ZIP 17K	8" (5 U)	5
RCHD1910BK1 RCHD1910CG1 RCHD1910LG1	Black Beige Light Gray	18K	ZIP 18K	10.5" (6 U)	5
RCHD1914BK1	Black Beige Light Gray	19K	ZIP 20K	14" (8 U)	6
RCHD1917BK1 RCHD1917CG1 RCHD1917LG1	Black Beige Light Gray	21K	ZIP 22K	17.5" (10 U)	7
RCHD1922BK1 RCHD1922CG1 RCHD1922LG1	Black Beige Light Gray	22K	ZIP 24K	22.75" (13 U)	9
RCHD1928BK1 RCHD1928CG1 RCHD1928LG1	Black Beige Light Gray	24K	ZIP 27K	28" (16 U)	12



Extra Panel Rails

- RCHS rack cabinets ship with two pair order below for extra mounting capabilities
- Sold in pairs
- Finished in rugged black textured powder paint
- Includes amhal strut mounting hardware (black clip nuts are not included)

Part Number	Use With Cabinet Panel Height
RCHR1908	8" (5 U)
RCHR1910	10.5" (6 U)
RCHR1914	14" (8 U)
RCHR1917	17.5" (10 U)
RCHR1922	22.75" (13 U)

RCHR1928 28" (16 U)



Extra Spring Nuts - Part Number 1421SN

- 1/4 20 Strut nut
- 1/4 20 x 1/2 bolt
- Used only in our RCHS & RCHV table top rack cabinets handy for mounting of other equipment to the horizontal struts
- Sold in packages of 8 (8 spring nuts and 8 bolts) as shown




Replacement Rubber Feet - Part Number 1421RC24


- RCHS rack cabinets ship with four feet included order these for replacement
- Sold in package of 20






TOP VIEW







BOTTOM VIEW